

SPECIFICATION CONTROL DRAWING

SCD

55PC0112


Title WIRE, RADIATION-CROSSLINKED, MODIFIED ETFE-INSULATED, LIGHTWEIGHT, GENERAL PURPOSE, 600 VOLT

Date 5-14-15

Revision F

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

CONDUCTOR - SILVER-COATED COPPER



INSULATION - RADIATION-CROSSLINKED,
MODIFIED ETFE

PART NUMBER 1/	WIRE SIZE (AWG)	CONDUCTOR STRANDING (number x AWG)	CONDUCTOR DIAMETER (inch)			FINISHED WIRE					
			LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft.)	DIAMETER (inch)			WEIGHT (lbs/1000 ft.)	
							LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC0112-26-*	26	19 x 38	.0175	.0183	.0191	38.4	.0291	.0305	.0319	1.23	1.34
55PC0112-24-*	24	19 x 36	.0225	.0233	.0241	24.3	.0341	.0355	.0369	1.81	1.93
55PC0112-22-*	22	19 x 34	.0285	.0293	.0301	15.1	.0401	.0415	.0429	2.69	2.83
55PC0112-20-*	20	19 x 32	.0365	.0375	.0385	9.19	.0481	.0495	.0509	4.11	4.27
55PC0112-18-*	18	19 x 30	.0452	.0464	.0476	5.79	.0573	.0590	.0607	6.27	6.56
55PC0112-16-*	16	19 x 29	.0514	.0527	.0538	4.52	.0646	.0665	.0684	8.01	8.33
55PC0112-14-*	14	19 x 27	.0644	.0659	.0674	2.88	.0789	.0810	.0831	12.39	12.81
55PC0112-12-*	12	37 x 28	.0825	.0845	.0865	1.90	.0974	.1000	.1026	19.17	19.71
55PC0112-10-*	10	37 x 26	.1050	.1070	.1090	1.19	.1220	.1260	.1300	30.68	31.70
55PC0112-8-*	8	133 x 29	.158	.163	.169	.658	.183	.188	.193	57.7	59.9
55PC0112-6-*	6	133 x 27	.198	.205	.212	.418	.225	.234	.243	89.1	94.1

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 2

Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
501 Oaksider Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297

© 2008-2015 Tyco Electronics Corporation. All rights reserved.

**WIRE RATINGS AND ADDITIONAL REQUIREMENTS****TEMPERATURE RATING: 200°C**

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level**COLOR: White preferred****CROSSLINKED VERIFICATION: $300 \pm 3^\circ\text{C}$ for 1 hour****IDENTIFICATION AND COLOR STRIPING DURABILITY:**

125 cycles (250 strokes) (minimum), 500 g weight

INSULATION ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)**INSULATION FLAWS:**

Spark Test, 3.0 kV (rms)

Impulse Dielectric Test, 8.0 kV (peak)

INSULATION THICKNESS: 0.006 in. (nominal)**SHRINKAGE: $230 \pm 3^\circ\text{C}$ for 1 hour, 0.125 inch (maximum) in 12 inches****VOLTAGE WITHSTAND (Post Environmental): 2500 volts (rms)****1/ PART NUMBER:**

The "*" in the part numbers on page 1 shall be replaced by a color code designator.

Example: AWG 22, white: 55PC0112-22-9

AWG 22, white with a black stripe: 55PC0112-22-90

1/ See footer section on page 1