

3153 00010044

(Home (/index.php?ci_id=3972&la_id=1) : Products (/products) : Sensors : Thermostats : 3153)

Distributor Inventory

Input part number for stock availability



3150 Series Low Silhouette Hermetic Thermostats

Actual product appearance may vary.

Narrow Your Search

Modify Your Search

Products

Technology

Industries Served

Sales & Service

Distributor Inventory

Overview

Specs

Documentation

Application Notes

Product Specifications	
Functional Properties	Open on rise
Reset Type	Automatic
Amperage	2.0 A resistive
Voltage	30 Vac/Vdc
Operating Temperature	-29 °C to 177 °C [-20 °F to 350 °F]
Environmental Exposure Range	-65 °C to 260 °C [-85 °F to 500 °F]
Open Temperature	15.6 °C [60 °F] max.
Close Temperature	4.4 °C [40 °F] min.
Dielectric Strength	MIL-STD-202, Method 301; 1250 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; 500 MOhm
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm max.
Hermetic Seal	MIL-STD-202, Method 112; Cond. C
Moisture Resistance	MIL-STD-202, Method 106
Shock	MIL-STD-202, Method 213; 100 G
Vibration	MIL-STD-202, Method 204; 20 G
Thermal Shock	MIL-STD-202, Method 107; Cond. B
Salt Spray	MIL-STD-202, Method 101; Cond. B
Housing Material	Steel housing hermetically sealed with glass-to-metal seal at terminal junction
Contact Material	Silver
Agency Approvals and Standards	Acceptance testing performed in accordance to Mil-PRF-24236, Table III
Mounting	No bracket
Series Name	3153

Product Search

Product Type: All Product Types

Industry: All Industries

New Products Only

Entire Product Catalog

My Links

eCOM Login (/index.php?ci_id=50629&la_id=1)
Request Access to eCOM (/ecom access request)
Rep/AD Portal Login (/index.php?ci_id=50606&la_id=1)
Rep/AD Portal Access Request (/index.php?ci_id=50630&la_id=1)
Sample Request (/samplerequest)
Digital U - HWL Learning Hub Login (/index.php?ci_id=50607&la_id=1)
Digital U - HWL Learning Hub Access Request (/index.php?ci_id=146099&la_id=1)
 <http://www.youtube.com/user/SensingAndControl>
 <http://twitter.com/HONSensorSwitch>
Supplier Microsite (/index.php?ci_id=50631&la_id=1)
Supplier Microsite (/index.php?ci_id=44887&la_id=1)

Literature and Media

Data Sheets (/white paper and technical data sheets library)
Videos (/videos)
Literature (/literature)
Literature Request (/index.php?ci_id=50636&la_id=1)
White Papers (/whitepapers)
Application Notes (/application notes)
Application Demos (/index.php?ci_id=141383&la_id=1)
CAD Renderings (/cad renderings)

Contacts

Customer Service (/index.php?ci_id=50608&la_id=1)
Technical Support (/index.php?ci_id=50609&la_id=1)
Global Sales & Service (/index.php?ci_id=50610&la_id=1)
Website Feedback (/index.php?ci_id=142628&la_id=1)

[Terms & Conditions \(/index.php?ci_id=2588&la_id=1\)](#)

[Privacy Statement \(/index.php?ci_id=2589&la_id=1\)](#)

[Site Map \(/sitemap\)](#)