



+ CONNECTORS

HSSDC2 CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
KIT,HSSDC2,PLUG,INFINIBAND
HSSDC/HSSDC2

1761070-1
TE Internal Number: 1761070-1

EU RoHS Compliant
EU ELV Compliant

Connector Style Plug
Number of Positions 7

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

KIT, HSSDC2 PLUG INFINIBAND
PDF (TIFF AVAILABLE)
English

CAD Files

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Customer View Model
2D_DXF.ZIP
English

3D PDF

PDF

English

Product Specifications

Application Specification

High Speed Serial Data Connector 2 (HSSDC2) Plug Assembly

PDF

English

Product Specification

High Speed Serial Data 2 Connector

PDF

English

Qualification Test Report

High Speed Serial Data 2 Connector

TIF

English

High Speed Serial Data 2 Connector

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

Crimping Die Assemblies 1583015-1, -2, -3, And 1583016-1 For High Speed Serial Data Connector 2 (HSSDC2)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Plug

Product Designation None

Product Type Connector

Configuration Features

Number of Positions 7

Body Features

Spring Plating Material Tin

Housing Features

Housing Material Die Cast Metal
Housing Plating Material Tin over Nickel over Copper

Dimensions

Cable Diameter Range 5.46 – 6.22 mm [.215 – .245 in]

Operation/Application

For Use With HSSDC2

Other

Spring Material Phosphor Bronze
Comment Does not include cable, overmold, wire organizer or plug PCB.

PRODUCT COMPLIANCE

+

Statement of Compliance

Statement of Compliance
PDF