

SERIES: VHB200W | DESCRIPTION: DC-DC CONVERTER

FEATURES


- up to 200 W isolated output
- industry standard half brick package
- 4:1 input range (10~36 V, 18~75 V)
- single output from 3.3~48 V
- 1,500 V isolation
- over current, over temperature, over voltage, and short circuit protections
- remote on/off
- efficiency up to 89%



MODEL	input voltage range (Vdc)	output voltage (Vdc)	output current max (A)	output power max (W)	ripple and noise ¹ max (mVp-p)	efficiency typ (%)
VHB200W-Q24-S3R3	10 ~ 36	3.3	50.0	165	100	87
VHB200W-Q24-S5	10 ~ 36	5	40.0	200	100	87
VHB200W-Q24-S12	10 ~ 36	12	16.7	200	150	86
VHB200W-Q24-S15	10 ~ 36	15	13.3	200	150	86
VHB200W-Q24-S24	10 ~ 36	24	8.3	200	240	87
VHB200W-Q24-S28	10 ~ 36	28	7.1	200	280	87
VHB200W-Q24-S48	10 ~ 36	48	4.2	200	240	86
VHB200W-Q48-S3R3	18 ~ 75	3.3	40	132	100	88
VHB200W-Q48-S5	18 ~ 75	5	40	200	100	89
VHB200W-Q48-S12	18 ~ 75	12	16.7	200	150	88
VHB200W-Q48-S15	18 ~ 75	15	13.3	200	150	88
VHB200W-Q48-S24	18 ~ 75	24	8.3	200	240	88
VHB200W-Q48-S28	18 ~ 75	28	7.1	200	280	88
VHB200W-Q48-S48	18 ~ 75	48	4.2	200	240	87

Notes: 1. ripple and noise are measured at 20 MHz BW with 10μF tantalum capacitor and 1μF ceramic capacitor across output

PART NUMBER KEY



INPUT

parameter	conditions/description		min	typ	max	units
operating input voltage			10	24	36	Vdc
			18	48	75	Vdc
under voltage lockout	power up	24 V input		9.5		Vdc
		48 V input		17.0		Vdc
	power down	24 V input		8.5		Vdc
		48 V input		16.0		Vdc
positive logic remote on/off ¹						
filter	Pi type					
Notes:	1. logic compatibility, open collector ref to -input Module ON, >3.5 Vdc or open circuit Module OFF, <1.8 Vdc					

OUTPUT

parameter	conditions/description		min	typ	max	units
line regulation	measured from high line to low line				±0.2	%
load regulation	measured from full load to zero load				±0.2	%
voltage accuracy					±1.5	%
transient response	25% step load change				500	µs
adjustability ²				±10		%
switching frequency	100% load, input voltage range			250		kHz
temperature coefficient				±0.03		%/°C
Notes:	2. trim-up: connect a resistor between the trim pin and +Sense trim-down: connect a resistor between the trim pin and -Sense					

PROTECTIONS

parameter	conditions/description		min	typ	max	units
over voltage protection	%Vo		115		140	%
short circuit protection	continuous					
current limit	% nominal output current		110		150	%
thermal shutdown case temp.				110		°C


SAFETY AND COMPLIANCE

parameter	conditions/description		min	typ	max	units
isolation voltage	input to output		1,500			Vdc
	input to case		1,500			Vdc
	output to case		1,500			Vdc
isolation resistance			10			MΩ
isolation capacitance				1,000		pF
safety approvals	certified to 60950-1: UL					
MTBF	as per MIL-HDBK-217F (Notice 1), GB, at 25°C			600,000		hours
RoHS compliant	yes					

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
case operating temperature	see derating curve	-40		100	°C
storage temperature		-55		105	°C
humidity	non-condensing			95	%


DERATING CURVE



MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	57.9 x 61.0 x 13.2 [2.28 x 2.40 x 0.52 inch]				mm
case material	aluminum baseplate with plastic case				
weight			114		g

MECHANICAL DRAWING



Note: All specifications measured at 25°C, nominal input voltage, and full load unless otherwise noted.

OUTPUT REMOTE SENSING

Remote sensing regulates output voltage at the point of load rather than at the module terminals, compensating for voltage drop across distribution wiring.

Figure 1




Figure 2




Table 1


PARAMETER	VALUE
Remote-sense compensation range	$[(+V_{out}) - (-V_{out})] - [(+Sense) - (-Sense)] \leq 10\% \text{ of } V_o(\text{nominal})$
Max sense wire length	400 mm
Sense wiring type	Twisted-pair or shielded wire
If sense unused	Connect +Sense to +Vout and –Sense to –Vout directly at the module; keep jumpers as short as possible; avoid loop wiring

Note: 1. If remote sense and trim are both used, the resulting output deviation is the larger of the two values, not their sum. $P_{out(max)} = V_o(set) \times I_o(max)$ is an absolute limit — in creasing V_o via sense/trim raises output power at constant current, so verify the module stays within rated power; decreasing V_o proportionally reduces $P_{out(max)}$, since $I_o(max)$ is fixed.


OUTPUT VOLTAGE ADJUSTMENT

Output may be trimmed ±10% via external resistor (fixed) or potentiometer (variable), connected to the Trim pin.

Method 1
Output Voltage Trim Circuit Configuration



Method 2
Output Voltage Trim Circuit Configuration with VR



$$R_{\text{TRIM}} = \left(\frac{5.11V_{\text{NOM}} (100 + \Delta\%)}{1.225 \times \Delta\% } - \frac{511}{\Delta\% } - 10.22 \right) (\text{K } \Omega)$$

Formula for Trim up
Vo: 3.3, 5, 12, 15, 24, 28V

$$R_{\text{TRIM}} = \left(\frac{511}{\Delta\% } \right) - 10.22 \text{ (K } \Omega)$$

Formula for Trim down
Vo: 3.3, 5, 12, 15, 24, 28V

$$R_{\text{TRIM}} = \left(\frac{20V_{\text{NOM}} (100 + \Delta\%)}{1.225 \times \Delta\% } - \frac{2000}{\Delta\% } - 40 \right) (\text{K } \Omega)$$

Formula for Trim up
Vo: 48V

$$R_{\text{TRIM}} = \left(\frac{2000}{\Delta\% } \right) - 40 \text{ (K } \Omega)$$

Formula for Trim down
Vo: 48V

$$V_{\text{OUT (desired)}} \Delta\% = \left(\frac{V_{\text{OUT}} - V_{\text{NOM}}}{V_{\text{NOM}}} \right) \times 100$$

Formula for Trim up

$$\Delta\% = \left(\frac{V_{\text{NOM}} - V_{\text{OUT}}}{V_{\text{NOM}}} \right) \times 100$$

Formula for Trim down

Table 2
Rtrim-down — Typical Values (kΩ)

Trim _{DOWN}	3.3	5	12	15	24	28	48
(%)	(V)	(V)	(V)	(V)	(V)	(V)	(V)
1%	500.8	500.8	500.8	500.8	500.8	500.8	1960
5%	92	92	92	92	92	92	360
10%	40.9	40.9	40.9	40.9	40.9	40.9	160

OUTPUT VOLTAGE ADJUSTMENT (CONTINUED)

Table 3
Rtrim-up — Typical Values (k Ω)

Trim _{DOWN}	3.3	5	12	15	24	28	48
(%)	(V)	(V)	(V)	(V)	(V)	(V)	(V)
1%	869.1	1585.4	4534.6	5798.5	9590.3	11275.6	77111
5%	176.7	325.6	938.8	1201.6	1990	2340.4	16017.1
10%	90.1	168.1	489.3	627	1039.9	1223.5	8380.4

Table 4
Recommended Resistor Values

V _{NOM}	R _{TOP}	R _{BOTTOM}	V _{REF}
(Vdc)	(k Ω)	(k Ω)	(k Ω)
3.3	9.1	7.5	10
5	13.7	5.6	10
12	30	4.3	20
15	36	3.9	20
24	43	2.7	20
28	51	2.67	20
48	68	2.0	20

Note (28V models): Trim-down is limited to –10% as standard; trim-up is constrained by input voltage — refer to Output Voltage Trim Limits vs. Input Voltage curves before setting VR upper limits.

EMC RECOMMENDED CIRCUIT

Figure 3
Connection Circuit For Conducted EMI Class A Testing




Table 5
EN 55032 Class A — Component Values by Model

MODEL	C1	C2	L1	L2
VHB200W-Q24-S3R3	47 μ F/100 V	47 μ F/100 V	0.5 mH	short
VHB200W-Q24-S5	82 μ F/100 V	82 μ F/100 V	0.5 mH	short
VHB200W-Q24-S12	120 μ F/100 V	120 μ F/100 V	0.5 mH	short
VHB200W-Q24-S15	47 μ F/100 V	47 μ F/100 V	0.5 mH	short
VHB200W-Q24-S24	100 μ F/100 V	100 μ F/100 V	0.5 mH	short
VHB200W-Q24-S28	100 μ F/100 V	100 μ F/100 V	0.5 mH	short
VHB200W-Q48-S3R3	47 μ F/100 V	47 μ F/100 V	0.1mH	short
VHB200W-Q48-S5	47 μ F/100 V	47 μ F/100 V	0.5 mH	short
VHB200W-Q48-S12	82 μ F/100 V	82 μ F/100 V	0.5 mH	short
VHB200W-Q48-S15	82 μ F/100 V	82 μ F/100 V	0.5 mH	short
VHB200W-Q48-S24	82 μ F/100 V	82 μ F/100 V	0.7 mH	short
VHB200W-Q48-S28	150 μ F/100 V	150 μ F/100 V	0.5 mH	short

EMC RECOMMENDED CIRCUIT (CONTINUED)

Figure 4
Class A circuit, 48V-output models, CY1/CY2




Table 6
EN 55032 Class A – 48V-Output Models (require additional C3, CY1, CY2)

MODEL	C1	C2	C3	CY1	CY2	L1
VHB200W-Q24-S48	100 μ F/100 V	100 μ F/100 V	100 μ F/100 V	680 pF/2KV	680 pF/2KV	1.0 mH
VHB200W-Q48-S48	100 μ F/100 V	100 μ F/100 V	100 μ F/100 V	680 pF/2KV	680 pF/2KV	1.0 mH

Note: C1, C2 = NIPPON CHEMI-CON KY series aluminum capacitors. C1/C2 correspond to input-side filter caps in the Class A test circuit (Figure, Section 10.2); L1/L2 correspond to the two series inductors in that same circuit.

Figure 5
Class B circuit, CY1–CY4




Table 7
EN 55032 Class B – Component Values by Model

MODEL	C1	C2	C3	CY1	CY2	CY3	CY4	L1
VHB200W-Q24-S24	120 μ F/100 V	120 μ F/100 V	10 μ F/50 V	1000 pF/2KV	NC	1000 pF/2KV	NC	0.5 mH
VHB200W-Q24-S48	82 μ F/100 V	82 μ F/100 V	4.7 μ F/100 V	1000 pF/2KV	680 pF/2KV	1000 pF/2KV	680 pF/2KV	0.45 mH
VHB200W-Q48-S12	120 μ F/100 V	120 μ F/100 V	4.7 μ F/100 V	1000 pF/2KV	NC	680 pF/2KV	NC	0.5 mH
VHB200W-Q48-S48	82 μ F/100 V	82 μ F/100 V	4.7 μ F/100 V	2200 pF/2KV	NC	2200 pF/2KV	680 pF/2KV	0.45 mH

Note: C1, C2 = NIPPON CHEMI-CON KY series aluminum capacitors; C3, CY1–CY4 = ceramic capacitors.

REVISION HISTORY

rev.	description	date
1.0	initial release	08/08/2008
1.01	new template applied	08/05/2011
1.02	add remote on/off control to the part number key	11/23/2011
1.03	features updated	12/20/2011
1.04	misc. updates and corrections	02/14/2012
1.05	V-Infinity branding removed	09/07/2012
1.06	updated spec	04/01/2013
1.07	company logo updated	02/09/2021
1.08	derating curve inserted	03/04/2021
1.09	company address updated	11/14/2024
1.10	datasheet updated	05/29/2025
1.11	MTBF added	05/21/2026
1.12	EMI/EMC, output remote sensing and output voltage adjustment added	07/10/2026

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC
a bel group

15575 SW Sequoia Pkwy #100
Portland, OR 97224
800.275.4899

Fax 503.612.2383
Belfuse.com
powersupport@belf.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.