



Part Number : [716612040](#)
Product Description : 1.27mm Pitch EBBI 50D Plug,
Right-Angle, 40 Circuits, 2.79mm PC Tail Length
Series Number : 71661
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[716612040_sd.pdf](#)
[PK-70873-084X-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[PS-71660-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	71661
Description	1.27mm Pitch EBBI 50D Plug, Right-Angle, 40 Circuits, 2.79mm PC Tail Length
Application	Board-to-Board, Wire-to-Board
Component Type	PCB Header
Product Name	EBBI
UPC	800754351850

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V

Physical

Breakaway	No
Circuits (Loaded)	40

Circuits (maximum)	40
Color - Resin	Black
Durability (mating cycles max)	2000
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.538/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.79mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Lead-Free Process Capability	SMC&WAVE
Max-Temp	235

Mates With / Use With

Mates with Part(s)

Description	Part Number
EBBI 50D Vertical PCB Receptacles	<u>71660</u>

This document was generated on May 27, 2026