

Part Number : 1202530673
Product Description : Contrinex Inductive Sensor, M8 Fully Stainless Steel, 3mm Operating Distance, Embeddable, PNP, NO, 3-pin M8 Connector, 60mm Housing Length
Series Number : 120253
Status : Obsolete
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : DW-AS-703-M8-673

Obsolete

Documents and Resources

Specifications

1202530673-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M8 Fully Stainless Steel, 3mm Operating Distance, Embeddable, PNP, NO, 3-pin M8 Connector, 60mm Housing Length
IP Rating	IP68, IP69K
Product Name	Contrinex
Type	Inductive
UPC	191130066131

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 15 Hz

Physical

Connection	Connector (M8, 3-pin)
Length	60mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel
Mounting Style	Embeddable
Net Weight	244.000/g
Operating Distance	3mm
Output	NO
Sensor Housing Size	M8
Temperature Range - Operating	-25° to +85°C

Obsolete

Downloaded from Arrow.com.

This document was generated on Sep 25, 2026

Obsolete

Downloaded from Arrow.com.