



**Part Number :** [1202530587](#)  
**Product Description :** Contrinex Inductive Sensor, M30 Fully Stainless Steel, 20mm Operating Distance, Embeddable, PNP, NO, 2m 3-wire PUR Cable, 50mm Housing Length  
**Series Number :** 120253  
**Status :** Not Recommended For New Design  
**Product Category :** Inductive and Photoelectric Sensors  
**Engineering Number :** DW-AD-703-M30



Documents & Resources

Specifications

[1202530585-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

#### UKCA - Declaration of Conformity

#### CE - Declaration of Conformity

---

## Part Details

### General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M30 Fully Stainless Steel, 20mm Operating Distance, Embeddable, PNP, NO, 2m 3-wire PUR Cable, 50mm Housing Length
IP Rating	IP68, IP69K
Product Name	Contrinex
Type	Inductive
UPC	191130070220

### Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 125 Hz

### Physical

Connection	Cable (PUR 2m, 3-wire)
Length	50mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel
Mounting Style	Embeddable
Operating Distance	20mm
Output	NO

Sensor Housing Size	M30
Temperature Range - Operating	-25° to +85°C

---

This document was generated on Sep 17, 2025