




Color: ■ red

Similar to illustration

Technical data	
Marking method	Thermal transfer
Marking	1 ... 10
Marking (number)	10
Marking direction	Horizontal marking
Marking color	black
Marking type	Numbers
Marking differentiation	Consecutive numbers per strip
Delivery form	Marker card
Delivery form configuration	10 strips with 10 markers per card
Flammability class per UL94	V2

Physical data	
Marker/strip width	5 ... 5.2 mm
Marker width	5 mm

Mechanical data	
Smear resistance	EN 60998-1:2004

Material data	
Color	red
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	8.8 g
Fire load	0.264 MJ



Commercial data		
PU (SPU)		50 (5) pcs
Packaging type		Box
Country of origin		DE
GTIN		4045454634131
Customs tariff number		49119900000

Product classification		
UNSPSC		55121731
eCl@ss 10.0		27-14-11-37
eCl@ss 9.0		27-14-11-37
ETIM 9.0		EC000761
ETIM 8.0		EC000761
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 793-5502/000-005	

CAD/CAE-Data

CAE data	
EPLAN Data Portal 793-5502/000-005	

Installation Notes

Application




Separating a strip from the WMB or WMB marker card.



Stretching a WMB marker strip.



Separating an individual marker from the WMB marker strip – for larger terminal blocks.



Snapping a marking strip into the marker slot.

Marking



Snapping a WMB marker strip into the marker slot of the double marker carrier.



Snapping a marking strip into the marker slot.