



Pushing Performance
Since 1945

PushPull V4 plug, RJ45, Cat.6A



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 145 1521
Specification	PushPull V4 plug, RJ45, Cat.6A
HARTING eCatalogue	https://b2b.harting.com/09451451521

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	RJ45
Element	Connector sets

Version

Termination method	Piercing termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Locking type	PushPull
Pack contents	incl. housing with RJ45 connector, shielding and cable gland

Technical characteristics

Conductor cross-section	0.08 ... 0.22 mm²
Conductor cross-section	AWG 28/7 ... AWG 24/7 Stranded
Wire outer diameter	1 mm
Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Tightening torque	1.3 ... 1.5 Nm
Limiting temperature	-40 ... +70 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	4.5 ... 10 mm
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 2h/axis 5.72 m/s² acc. to IEC 61373 Category 1 Class B
Shock resistance	25 g / 11 ms, 3 shocks / axis and direction 5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4) EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL



Pushing Performance
Since 1945

Commercial data

Packaging size	10
Net weight	4.939 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140223745
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)