


REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	FIRST RELEASE	Jul.31,18	White	Tommy
A2	-	UPDATED DRAWING	Sep.27,18	White	Tommy
A3	-	UPDATED DRAWING	Dec.11,18	White	Tommy







NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:
   1.1 HOUSING: THERMOPLASTIC UL94 V0
   1.2 SEAL: SILICONE RUBBER
   1.3 CONTACT: COPPER ALLOY,SILVER PLATED

2. SPECIFICATIONS:
   2.1 CURRENT RATING: 50 mm² @180 AMPS
   35 mm² @130 AMPS
   2.2 OPERATING VOLTAGE: 1000V AC/DC
   2.3 CONTACT RESISTANCE:0.3mΩ
   2.4 OPERATING TEMPERATURE: -55℃ TO +125℃
   2.5 DEGREE OF PROTECTION: IP67 (MATED CONDITION)
   2.6 MATING CYCLE DURABILITY: 50 CYCLES
   2.7 RoHS COMPLIANT

3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

ITEM	P/N	WIRE RANGE	NOTE
1	ATHP041P08NN-50	50 mm²	BLACK(SHELL)
2	ATHP041P08NN-35	35 mm²	BLACK(SHELL)
3	ATHP041P08NN-50-ORG	50 mm²	ORANGE(SHELL)
4	ATHP041P08NN-35-ORG	35 mm²	ORANGE(SHELL)

	PART NUMBER	DESCRIPTION	ITEM
QUANTITY	MATERIALS LIST		

UNLESS OTHERWISE SPECIFIED
1) All dimensions are in metric(mm).
2) Tolerances are as follows:
1 PL DEC ±0.30 | Fractions ±1/64
2 PL DEC ±0.15 | Angles ±1°
3 PL DEC ±0.08
3) Note reference = X

MATERIAL SPECIFICATIONS:

PROCESS SPECIFICATIONS:

NEXT ASS'Y:

SIGNATURES		DATE
DRAWN:	White	Dec.11,18
CHECKED:	Tod	Dec.11,18
ENGINEER:		
APPROVAL:	Tommy	Dec.11,18
CUSTOMER:		

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Amphenol

Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036

ATHP,8MM,
STRAIGHT RECEPTACLE

SIZE	TYPE	DWG NO:	REVISION
B	C-	ATHP041P08NN-xx-x	A3

SCALE NONE | SHEET 1 OF 1

TITLE: ATHP,8MM,STRAIGHT RECEPTACLE
DWG NO: ATHP041P08NN-xx-x
REV: A3
SH: 1
OF: 1

Downloaded from Arrow.com.