
This browser does not have Java enabled.

2-1986711-3 Product Details



Terminal Block Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Type of Connector = Spring (Straight)
- Not Shrouded
- Housing Color = Green
- Side Stackable

View all Features

2-1986711-3

TE Internal Number: 2-1986711-3

Active

View 3D PDF

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- SPRING TYPE. SIDE WIRE ENTRY TERMINAL BLOCK SIDE STA... (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files: (CAD Format & Compression Information)
- 2D Drawing (DXF, Version A)
- 3D Model (IGES, Version A)
- 3D Model (STEP, Version A)

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Connector
- Type of Connector = Spring (Straight)
- Shrouded = No
- Mount Angle = Vertical
- UL File Number = E60677

Electrical Characteristics:
- Current Rating, Max. (A) = 16
- Voltage (VAC) = 300

Dimensions:
- Pin Length (mm [in]) = 3.50 [0.138]

Body Features:
- Side Stackable = Yes
- Wire Entry Diameter (Solid Wire) (mm²) = 0.05 - 3.00
- Wire Entry Diameter (Stranded Wire) (mm²) = 0.05 - 3.00
- Wire Entry Angle = Side
- Interlock = Without
- Wire Range (mm [AWG]) = 0.05-3.00² [30-12]
- Lever Color = White

Contact Features:
- Threaded Flange = Without
- Contact Plating, Mating Area, Material = Tin over Copper Alloy

Housing Features:
- Housing Color = Green
- Centerline (mm [in]) = 5.00 [0.197]
- Housing Material = Polyamide

Configuration Features:
- Screw Flange = Without
- Number of Positions = 23
- Number of Rows = Single

Industry Standards:
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:
- Brand = TE Connectivity

© 2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved

Downloaded from Arrow.com.