
Part Number : 1054312407
Product Description : Nano-Fit Vertical Header, Surface Mount, 2.50mm Pitch, Single Row, 7 Circuits, 0.76µm Gold (Au) Plating, with Pick-and-Place Tape, Lubricated, Natural, Glow-Wire Capable
Series Number : 105431
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

1054312407_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

AS-105405-001-001.pdf

1054051000-PS-CH-000.pdf

1054051000-PS-ES-000.pdf

1054051000-PS-SK-000.pdf

PS-105405-001-001.pdf

1054050000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

Downloaded from Arrow.com.

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	105431
Description	Nano-Fit Vertical Header, Surface Mount, 2.50mm Pitch, Single Row, 7 Circuits, 0.76µm Gold (Au) Plating, with Pick-and-Place Tape, Lubricated, Natural, Glow-Wire Capable
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	Nano-Fit
UPC	191130009954

Agency

UL	E29179

Downloaded from Arrow.com.

Electrical

Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Natural
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	1.170/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Robotic Placement	Vacuum Pick-Up Tape
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Surface Mount

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Single Row, 7 Circuits, Natural, Glow-Wire Capable	1053072207
Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Single Row, 7 Circuits, Natural, Glow-Wire Capable, for UL 1569/1007 Wire	2263542207

Downloaded from Arrow.com.