

Part Number: KTIR0121DS


Features

- High sensing accuracy
- High current transfer ratio
- Both-sides mounting type
- RoHS compliant.

Applications

- OA equipment, such as floppy disk drives, printers, facsimiles, etc
- VCRs

Package Dimensions



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is ± 0.25 (0.01") unless otherwise noted.
3. Lead spacing is measured where the leads emerge from the package.
4. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

Absolute Maximum Ratings ($T_A=25^\circ\text{C}$)

Parameter		Symbol	Rating	Unit
Input	Forward current	I_F	50	mA
	Reverse voltage	V_R	6	V
	Power dissipation	P_D	75	mW
	Peak Forward Current (Pulse Width $\leq 100\mu\text{s}$, Duty Cycle = 1%)	I_{FP}	1	A
Output	Collector-emitter voltage	V_{CEO}	35	V
	Emitter-collector voltage	V_{ECO}	6	V
	Collector current	I_C	40	mA
	Collector power dissipation	P_C	75	mW
Operating temperature		T_{opr}	-40~+85	$^\circ\text{C}$
Storage temperature		T_{stg}	-40~+85	$^\circ\text{C}$
Soldering temperature (1/16 inch from body for 5 seconds)		T_{sol}	260	$^\circ\text{C}$



Electro-optical Characteristics(Ta=25°C)

Parameter		Symbol	Conditions	Min.	Typ.	Max.	Unit
Input	Forward voltage	V_F	$I_F=20\text{mA}$	1.0	1.2	1.5	V
	Peak forward voltage	V_{FM}	$I_{FM}=0.5\text{A}$	—	2	3	V
	Reverse current	I_R	$V_R=6\text{V}$	—	—	10	μA
Output	Collector dark current	I_{CEO}	$V_{CE}=10\text{V}, I_F=0\text{mA}$	—	—	10^{-6}	A
Transfer Characteristics	Current transfer ratio		$V_{CE}=2\text{V}$ $I_F=1\text{mA}$	—	600	—	%
	Collector-emitter saturation voltage		$I_F=2\text{mA}$ $I_C=1\text{mA}$	—	—	1.0	V
	Response time	Rise time	$V_{CE}=2\text{V}$ $I_C=10\text{mA}$ $R_L=100\Omega$	—	90	400	μSec
		Fall time		—	80	300	μSec

Fig.1 Forward Current vs. Forward Voltage




Fig.2 Collector Current vs. Forward Current




Fig.3 Collector Current vs. Collector-emitter Voltage




Fig.4 Collector Current vs. Ambient Temperature




Fig.5 Collector-emitter Saturation Voltage vs. Ambient Temperature




Fig.6 Relative Collector Current vs. Shield Distance(1)




Fig.7 Relative Collector Current vs. Shield Distance(2)






Fig.8 Response Time vs. Load Resistance




Test Circuit for Response Time



PACKING & LABEL SPECIFICATIONS

KTIR0121DS



Kingbright	
P/NO: KTIRxxx	
QTY: 200 pcs	Q.C. Q C XX XX XX PASSED
S/N: XXXX	
CODE: XXX	
LOT NO:	
	
RoHS Compliant	

Terms and conditions for the usage of this document

1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
6. All design applications should refer to Kingbright application notes available at http://www.kingbright.com/application_notes