


1721105-4 Product Details



1721105-4

TE Internal Number: 1721105-4

✔ [Active](#)

Industrial Relays (General Purpose)

✔ [Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- PCD Series
- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Contact Current Rating = 15 Amps.
- Monostable Coil Magnetic System
- Without Coil Suppression Diode

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [PCD-D2M SPEC,000 CUSTOMER DRAWING](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [PCD-112D2M,000](#) (PDF, Japanese)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Schematic](#)
- [Wiring Diagram](#)
- [PCB Layout \(Bottom Surface\)](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Type](#) = Through Hole

Electrical Characteristics:

- [Contact Current Rating \(Amps.\)](#) = 15
- [Coil Resistance \(Ω\)](#) = 720
- [Coil Power, Nominal \(mW\)](#) = 200
- [Actuating System](#) = DC
- [Input Voltage \(VDC\)](#) = 12

Body Related Features:

- [Series](#) = PCD
- Polarized = No

Contact Related Features:

- [Mounting Options](#) = PC Board
- [Enclosure](#) = Flux-Tight
- FCC Part 68 Isolation = No
- Relay Type = PCB
- [Contact Base Material](#) = Silver Tin Oxide
- Approx. Dimensions (L x W x H) (mm [in]) = 23.00 x 16.10 x 10.20 [.906 x .634 x .402]
- Approved Standards = UL Recognized, CSA Certified, TUV Approved

Configuration Related Features:

- [Contact Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Coil Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = OEG