





POS.	A -0.76	B -0.25	C	PART-NO.
9	31.19	16.46	25.00 ± 0.12 ± 0.13	242C17660X
15	39.52	24.79	33.30 ± 0.15 ± 0.1	242C17670X
25	53.42	38.50	47.04 ± 0.13	242C17680X
37	69.70	54.96	63.50 ± 0.13	242C17690X



NOTES:

1. RoHS COMPLIANT
2. SUITABLE FOR WAVESOLDERING
3. METALSHIELDS: STEEL; min. 315µin TIN over 40-80pin NICKEL
4. INSULATORS: HIGH TEMPERATURE PLASTIC UL 94 V-0, BLACK
5. CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD OVER min. 50µin NICKEL
6. METAL BRACKET: ZINC DIE CAST; 300µin COPPER/40-120µin NICKEL/120-200µin TIN
7. THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
8. FIXING-PLATE: PBT GF UL 94 V-0, BLACK
9. P.C.B. HOLE DRILLINGS ON SHEET 2
10. CAPACITANCE: 1300pF $\pm 20\%$
11. DIELECTRIC WITHSTANDING VOLTAGE: 424 VDC
12. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
13. CONNECTOR IS PART MARKED: **PART-NO. CONEC ABC**

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACIOM # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACIOM # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND


rev.	description	date	name
a	Origin		

tolerance	dim. in mm
2008	date
drawn	24.10. Lehmenkühler
appd.	24.10. Mickenbecker
norm	DIN 41652
d-old	


scale:	2:1 (5:1)
material:	SEE NOTES
title:	
D-SUB FILTER FEMALE 90°	
9-37pos. 0.318inch	
with threaded insert, metal bracket and snap	
dwg no:	AutoCAD 2006
24K3IW0A	
part no:	SEE TABLE

DIN-A
3
sh:1/2


9 pos.




15 pos.



25 pos.



37 pos.



used for: D-SUB FILTER

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

tolerance				dim. in mm	
2008	date	name	drawn	24.10.	Lehmenkühler
appd.	24.10.	Mickenbecker	norm	DIN 41652	
d-old					
a	Origin				
rev.	description	date	name		

CONEC

scale: 2:1	material: SEE SHEET 1
title: P.C.B. HOLE DRILLINGS	
D-SUB FILTER FEMALE 90° 9-37pos. 0.318inch with threaded insert, metal bracket and snap	
dwg no: AutoCAD 2006	DIN-A 3
sh:2/2	
part no: SEE SHEET 1	