



Part Number : [511910200](#)
Product Description : 2.50mm Pitch Mini-Latch
Wire-to-Wire and Wire-to-Board Receptacle Housing,
with Guide Rails, 2 Circuits
Series Number : 51191
Status : Not Recommended For New Design
Product Category : Connector Housings



Documents and Resources

Drawings

[511910200_sd.pdf](#)
[511910200_stp.zip](#)

Specifications

[511910000-AS-000.pdf](#)
[511919200-SPK-200.pdf](#)
[2055050000-PS-000.pdf](#)
[511910000-PS-000.pdf](#)
[PS-51191-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	51191
Description	2.50mm Pitch Mini-Latch Wire-to-Wire and Wire-to-Board Receptacle Housing, with Guide Rails, 2 Circuits
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Name	Mini-Latch
UPC	800753327702

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	276.600/mg
Number of Rows	1

Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Latch / KK Single Row Vertical Headers	<u>5045</u>
Mini-Latch / KK Single Row Right-Angle Headers	<u>5046</u>
Mini-Latch Single Row Plug Housings	<u>5240</u>

Use with Part(s)

Description	Part Number
Mini-Latch Female Crimp Terminals	<u>50802</u>

This document was generated on May 19, 2026