




REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	05/12/22	LCHAN




FRONT VIEW



SIDE VIEW



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)



RECOMMENDED PANEL CUTOUT

MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL94V-0

CONTACTS:

PHOSPHOR BRONZE

PLATING: REFER PART NUMBER FOR GOLD
THICKNESS ON MATING SURFACES.

50 μ " [1.27 MICRONS]

MIN. NICKEL UNDERPLATE.

100 μ " [2.54 MICRONS]

MIN. MATTE TIN OR GOLD FLASH ON CONTACT TAILS.

PART NUMBER: RJE05-166-0X10

GOLD PLATING

1 = 6 μ INCH

2 = 15 μ INCH

3 = 30 μ INCH

4 = 50 μ INCH

DRAWN Chigow	DATE 05/12/22
DESIGNED	
CHECKED PAULW	05/12/22
I. E. APPRD.	
Q. A. APPRD.	
DWG. APPRD.	
ENG. REL. NO.	
REF.	
DIMENSIONS ARE IN	CODE ID. NO.
mm	03554

Amphenol Canada Corp.

TITLE RJE05 SERIES MODULAR JACK,
6 POSITION, 6 CONTACTS, UNSHIELDED,
ULTRA LOW PROFILE-ROHS COMPLIANT

DWG. DRAWING NO. P-RJE05-166-0X10 REV. A

SCALE WT. SURF. SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.