



REVISION RECORD		
REV	DESCRIPTION	DRFT



NOTES:

MECHANICAL CHARACTERISTICS:

- 1.MATING FORCE: 3.57 Kg Max.
- 2.UNMATING: 1.0~1.6 Kg.
- 3.LIFE TEST: 10000 CYCLES

ELECTRICAL CHARACTERISTICS:

- 1.CURRENT RATING: 1.5A
- 2.CONTACT RESISTANCE: 30mΩ MAX.
- 3.DIELECTRICAL WITHSTANDING: 100V AC/1min.
- 4.INSULATION RESISTANCE: 100MΩ Min.

MATERIAL:

- 1.PLASTIC: LCP WITH 30% GF, UL 94V-0, Black.
- 2.TERMINAL: PHOSPHOR BRONZE, 0.2 THICKNESS.
- 3.TERMINAL PLATING:

UNDERPLATING ALL OVER NICKEL 50u"MIN.

CONTACT PLATING GOLD PLATING 15u"MIN

OTHER AREA GOLD PLATING 1u"MIN,

4.SHIELD: STEEL 0.3 THICKNESS.




5.SHIELD PLATING:


UNDERPLATING ALL OVER CU 20u"MIN

PLATING ALL OVER NICKEL 50u"MIN.






OTHERS:

- 1.OPERATION TEMPERATURE: -20℃ to +80℃




DETACHED LISTS	MM (INCH)		DFTD Roy	DATE 11/20/2012	 Pulse Electronics		RoHS Compliant		
	TOLERANCES EXCEPT AS NOTED		CHKD	DATE					
	MM		APPVL	DATE	TITLE USB 3.0 MICRO BF SMD TYPE				
	. ± 0.35		MATERIAL :						
	.0 ± 0.25								
	.00 ± 0.15								
	.000 ± 0.05								
	ANGLES: X:±1° X.X°±0.5°		QT'Y :	DRAWING NO. E8110-030-01				SIZE	REV
	 THIRD ANGLE PROJECTION		FINISH :	/PART NO. E8110-030-01				A3	01
			SCALE : 1:1	DO NOT SCALE DRAWING				SHEET 1	OF 2

REVISION RECORD		
REV	DESCRIPTION	DRFT



USB 3.0 Micro BF SMD TYPE+CAP

DETACHED LISTS	MM (INCH)		DFTD Roy	DATE 11/20/2012		RoHS Compliant		
	TOLERANCES EXCEPT AS NOTED		CHKD	DATE				
	MM			APPVL	DATE	TITLE USB 3.0 MICRO BF SMD TYPE		
	. ± 0.35		±					
	.0 ± 0.25		±					
	.00 ± 0.15		±					
	.000 ± 0.05		±					
ANGLES: X° ±1° X.X° ±0.5°		QT'Y :		DRAWING NO. E8110-030-01		SIZE	REV	
		FINISH :		/PART NO. E8110-030-01		A3	01	
THIRD ANGLE PROJECTION		SCALE : 1:1		DO NOT SCALE DRAWING		SHEET 2	OF 2	