


**Part Number :** [467083212](#)

**Product Description :** EXTreme Ten60Power Terminal Position Assurance (TPA) Retainer, for Assembly with 12 Signal / 2 Power Circuits

**Series Number :** 46708

**Status :** Active

**Product Category :** Connector Accessories



---

## Documents and Resources

### Drawings

[467083212\\_sd.pdf](#)

[PK-46708-0002-001.pdf](#)


### Specifications

[PS-173693-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Accessories
Series	46708
Description	EXTreme Ten60Power Terminal Position Assurance (TPA) Retainer, for Assembly with 12 Signal / 2 Power Circuits
Component Type	Terminal Position Assurance (TPA)
Keyword	Ten60
Product Name	EXTreme Ten60Power
UPC	889056277624

### Physical

Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	1.082/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

## Mates With / Use With

### Use with Part(s)

Description	Part Number
EXTreme Ten60Power Wire-to-Board Receptacle Housings	<u>172510</u>
EXTreme Ten60Power Panel-to-Board Receptacle Housings	<u>172512</u>

---

This document was generated on Apr 30, 2026