Pushing Performance
Since 1945

D-Sub F AWG 22-26 HMC contact Cat. 7 mod



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 200 5476
Specification	D-Sub F AWG 22-26 HMC contact Cat. 7 mod
HARTING eCatalogue	https://harting.com/09932005476

Identification

Category	Contacts
Series	D-Sub
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Female

Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm²
Conductor cross-section [AWG]	AWG 26 ... AWG 22
Transmission characteristics	Cat. 7_A
Contact resistance	≤10 mΩ
Mating cycles	≥10,000

Material properties

Surface (contacts)	HMC gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	100
Net weight	0.31 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140229235
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.