





SECTION E-E
SCALE 2.000
BOARD RETENTION PINS

NOTE :

- NOTE:
1. MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL 94 V-O FLAME RETARDANT.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
PLATING SPEC AS BELOW:
Ni 50u" UNDER PLATED.
Au 30u" OVER CONTACT AREA.(ONE SIDE)
MATTE TIN 120u" OVER SOLDERING AREA.
2. PACKING SPEC. GS-14-937
3. PRODUCT SPEC. GS-12-338.
4. MANUFACTURER'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.
5. PART NUMBER 10046971-054LF MEETS EUROPEAN UNION DIRECTIVE AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS
IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.

spec ref *				dr Hai-Ling Liu		2015/07/20		projection				MM		size A4		scale 1.000			
tolerance std TOLERANCES UNLESS OTHERWISE SPECIFIED				eng Hai-Ling Liu		2015/07/29						ecn no -							
				chr Terris Liu		2015/07/29						rel level Released							
				appr Pei-Ming Zheng		2015/07/29		product family											
surface ✓		linear		0.X		±0.5				title POWER EDGE CONNECTOR VERTICAL TYPE (25PX2)						dwg no 10046971-054		rev A	
				0.XX		±0.25													
				0.XXX		±0.1													
		angular		0°		±2°		www.fci.com		cat. no. *		Product - Customer Drw						sheet 1 of 2	

