

BA14E6M, Vinyl Ring Terminal For 16 - 14 AWG (Tape Mounted)

By Burndy
Catalog # [BA14E6M](#)



Vinyl Ring Terminal For 16 - 14 AWG (Tape Mounted)

Features

- Vinyl Ring Terminal banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	<ul style="list-style-type: none"> • 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	<ul style="list-style-type: none"> • 16 AWG • 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type

Ring Terminal

Dimensions

Dimension - Z inch	0.18 in
Dimension - Pad Width inch	0.25 in
Length	0.74 in
Dimension - Hole Size fraction	3/20
Dimension - Bolt Size fraction	#6
Dimension - Hole Size inch	0.15 in
Dimension - Stud Size inch	#6
Dimension - Length Overall inch	0.74 in
Width	0.26 in
Height	0.26 in
Dimensions	0.74 in x 0.26 in x 0.26 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Ring
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation Type	Y
Type	Ring Tongue
UPC 12 Digit	781810028971
UPC 14 Digit GTIN	00781810028971
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810028971

Logistics

Minimum Pack Quantity	2000
-----------------------	------

Product Assets

[Catalog \[English\]](#)