
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		NEW RELEASE	10MAR2015	RRN	PS




NOTES:
1. MATERIALS & FINISH
   HOUSING : PA HIGH TEMP 30GF V0, COLOUR: BLACK
   CONTACT : Cu ALLOY
   PLATING : LEAD FREE TIN OVER NICKEL UNDERPLATE

2. ELECTRICAL
   RATED VOLTAGE: 300V
   RATED CURRENT: 12A
   CONTACT RESISTANCE: <15 mOhm
   INSULATION RESISTANCE: >1000 MOhm (500V DC)

3. OPERATING TEMPERATURE RANGE: -40°C TO +110°C

4 TOLERANCE NOT CUMULATIVE.



-3 AS SHOWN

DIM OF "A"	NO OF POS.	PART NUMBER
35.00	8	1986707-8
25.00	6	1986707-6
15.00	4	1986707-4
10.00	3	1986707-3
5.00	2	1986707-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.2
2 PLC ±0.15
3 PLC ±-
4 PLC ±-
ANGLES ±2°

MATERIAL: SEE NOTE -

FINISH: - -

DWN R R NAYAK 10MAR2015
CHK PRASHANTH S 13MAR2015
APVD PRASHANTH S 13MAR2015
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME HEADER, SIDE STACKABLE, PITCH 5mm STRAIGHT, SMD
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1986707	-

Customer Drawing | SCALE 6:1 | SHEET 1 OF 1 | REV A

Downloaded from Arrow.com.