



LB1836MEVB: Bidirectional Motor Driver IC Evaluation Board

The LB1836M is 2-channel low-voltage, low saturation voltage type bidirectional motor driver IC that is optimal for use as a 2-phase stepping motor driver in printers, floppy disk drives, and cameras and other portable equipment. The output circuits are of the bipolar type, with pnp transistors in the upper side and npn transistors in the lower side, and they achieve low saturation output and low power characteristics despite being provided in a miniature package.

The LB1836M can directly control a motor from signals from a microcontroller. The LB1836M is ideally suited for the stepping motor, two phase excitation, and 1-2 phase excitation drive.

The LB1836M includes a built-in thermal shutdown circuit so that IC scorching or burning is prevented in advance, even if the IC outputs are shorted. Additionally, the MFP-14S miniature package used supports reduced-space mounting.



Features and Applications

Features

- Low voltage operation (2.5V min)
- Low saturation voltage (upper transistor + lower transistor residual voltage ; 0.40V typ at 400mA)
- Parallel connection (Upper transistor + lower transistor residual voltage ; 0.5V typ at 800mA)
- Separate logic power supply and motor power supply
- Brake function
- Spark killer diodes built in
- Thermal shutdown circuit built in
- Compact package (14-pin MFP)

Evaluation/Development Tool Information

Product	Status	Compliance	Short Description	Parts Used	Action
LB1836MEVB	Active		Bidirectional Motor Driver IC Evaluation Board	LB1836M-TLM-E	» Contact Local Sales Office » Inventory

Technical Documents

Type	Document Title	Document ID/Size	Rev
Eval Board: BOM	LB1836MEVB Bill of Materials	LB1836MEVB_BOM.PDF - 15 KB	0
Eval Board: Gerber	LB1836MEVB Gerber Layout Files (Zip Format)	LB1836MEVB_GERBER.ZIP - 102.0 KB	0
Eval Board: Schematic	LB1836MEVB Schematic	LB1836MEVB_SCHEMATIC.PDF - 132 KB	0
Eval Board: Test Procedure	LB1836MEVB Test Procedure	LB1836MEVB_TEST_PROCEDURE.PDF - 228 KB	1

Previously Viewed Products

Select Product... [Clear List](#)

Design Support

[Technical Documentation](#)

[Design Resources & Documents](#)

[Technical Support](#)

[Sales Support](#)

