




## Material Datasheet

20.03.2023

**HFT-A-2.4/1.2**  
Article Number 305-02406



Material: Polyolefin, cross-linked (PO-X)  
Colour: Blue (BU)

Supplied Ø D min.: 2.4 mm  
Recov. Ø d max.: 1.2 mm  
Wall (WT): 0.50 mm  
Shrink Ratio: 2:1  
Longitudinal Change After Shrinkage: -5% max.  
Min. Shrink Temperature - °C: +135 °C

Test Method

Flammability: self-extinguishing, UL 224 VW-1  
Operating Temperature : -55 °C to +135 °C  
Heat Shock Test: 4h/200°C  
Tensile Strength at Heat Shock: 13 MPa  
Elongation at Heat Shock: 390 %  
Behaviour At Low Temperature: not cracking

IEC 60684-2

Dielectric Strength: 21 kV/mm  
Insulation Class: B (VDE 0530)  
Tensile Strength: 14 MPa  
Elongation at break: 400%  
Specifications: CLASS 903201, UL 224, VG 95343-5:2016-10

IEC 60684-2

IEC 60684-2

IEC 60684-2



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved