

[Home](#) | [Sign In](#) | [Site Map](#) | [Contact Us](#)

Cannon VEAM BIW

SEARCH [About ITT](#)[Products](#)[Design Center](#)[Literature](#)[News & Events](#)[Search Tools](#)[Global Sales Support](#)[Home](#) > [Search Tools](#) > [Part Number](#)

Part Number Search

You Searched For:

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.
ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.

[Sales Support](#)[Product Overview](#)[Stock Check](#)[Product Home](#)

Our Catalog Part Number: DAMN-15P-N-K127

Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M



YES RoHS compliant =

material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC

YES RoHS compatible =

Compatible with lead free soldering process

Export Compliance



Country of Compliance

United States

Export Compliance Notes

Commercial Shipments "C"

Controlled by the US Department of Commerce.

Product Datasheet

General
Wire Gauge Range AWG
Mating Cycles
Contact Arrangement
Dielectric Withstanding Voltage
Current Rating
Contact Resistance
Operating Temperature
Salt Spray Test
Shell Material
Shell Finish
Insulator Material
Insulator Color
Gender
Contact Type
Contact Material
Contact Finish
Hardware

D*M High reliable D-Sub Connectors
AWG 20-28
200
15 contacts size 20
1000 VAC at sea level
7.5 A max
7.5 milli Ohm max
-55°/+125°
20 hours
steel
Tin over nickel plating
Thermoplastic, type PCT UL 94V-0
black
Pin
Straight PCB
copper alloy
30 Micro-inch gold
.300? (7.6mm) Standoff, 4-40 Screwlock, Boardlock

[Home](#) | [About ITT](#) | [Products](#) | [Design Center](#) | [Literature](#) | [News & Events](#) | [Search Tools](#) | [Global Sales Support](#)[Channel Partners Sign-In](#)[Legal Disclaimer](#) | [Privacy Policy](#) | [Terms & Conditions](#) |  [Provide Website Feedback](#)

© 2010 ITT Corporation. All rights reserved.