

■Laser Diodes

◆Package Lineup

· Can

① ø9 mm Can

② ø5.6 mm Can

③ ø3.8 mm Can

④ ø3.3 mm Can



· Frame

⑤ t1.8 mm Frame



◆Specifications

<High Output Laser Diodes>

(Tc = 25°C)

Package	Model No.	Wavelength (band) λ_p (nm)	Absolute maximum ratings ^{*1}		Characteristics								Emitter Quantity	Terminal connections	Applications				
			Iop (mA)	Top (°C)	Po (mW)	Ith (mA)	Iop (mA)	Vop (V)	η_d (mW/mA)	λ_p (nm)	$\theta_{//}^{*2}$ (°)	$\theta_{\perp}^{*2}$ (°)							
① ø9 mm Can	★GH04C05B9G	440	3 500	0 to +60	5 000	350	3 000	4.7	1.9	(tbd)	(tbd)	(tbd)	1	9	Display, etc.				
	☆GH04C03A9G	455	2 800	0 to +60	3 500	260	2 100	4.7	1.9	455	10 ⁻³	41 ⁻³	1	9					
	★GH04C05A9G		(tbd)	(tbd)	5 000	400	3 000	4.25			(tbd)	(tbd)							
	☆GH05C01A9G	520	1 400	0 to +60	600	220	1 100	5.2	0.65	520	13 ⁻³	45 ⁻³	1	(tbd)					
	★GH05C01B9G		(tbd)		1 000	(tbd)	(tbd)	(tbd)	(tbd)	(tbd)	(tbd)								
	★GH06C01A9G	638	(tbd)	−10 to +45	1 200	380	1 400	2.25	(tbd)	640	5 ⁻³	36 ⁻³	1	9					
	★GH06C02A9G		—		2 100	550	2 350	2.3											
	★GH06C02B9G				2 500	500	2 700												

*1 The absolute maximum ratings are the limits that are not to be exceeded under any condition whatsoever, whether in testing or in actual use.

*2 Full angle of 50% peak intensity.

*3 Full angle of 1/e² peak intensity.

<Multi-chip laser diodes>

(Tc = 25°C)

Package	Model No.	Wavelength (band) λ_p (nm)	Light output P _o (W)	Applications
Multi-chip package	★GH7AB95AM8	455	95	Projector, etc
	★GH7BB18AM8	520	18	
	★GH7CB43AM8	638/640	43	

Notice

In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc.

Except where specially indicated, models listed on this page comply with the EU RoHS Directive*. For details, please contact SHARP.
*EU RoHS Directive: EU legislation restricting the use of lead, cadmium, hexavalent chromium, mercury, specific brominated flame retardants (PBB and PBDE), and phthalates (DEHP, BBP, DBP, DIBP).

Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

<Laser Diodes for Automotive> *Consumer use possible

Package	Model No.	Wavelength (band) λ p (nm)	Absolute maximum ratings ^{*1}		Characteristics at 25°C								Built-in monitor PD	Terminal connections	Applications				
			Tc (°C)	Po (mW)	Po (mW)	Ith (mA)	Iop (mA)	Vop (V)	η d (mW/mA)	λ p (nm)	θ ^{*2} (°)	θ _⊥ ^{*2} (°)							
② ϕ 5.6mm Can	★GH0451AA2H	455	-40	55	100	28	105	5.4	1.3	455	9	22	—	8	Display, etc.				
			-10	105															
			+70	105															
			+95	55															
	★GH0451CA2H		-40	(tbd)	120		120	5								8	22	—	8
			-10	125															
			+70	125															
			+95	55															
	★GH0521AA2H	520	-40	55	100	70	210	6.5	0.7	520	8	22	—	8					
			-10	105															
			+50	105															
			+95	55															
	★GH0521GA2H		-40	(tbd)	160		310	6	0.65							8	22	—	8
			+10	165															
			+40	165															
			+95	55															
	★GH0632BA2G	638	-40	105	200	55	230	2.65	1.15	639	8	15	—	9					
			-20	150															
			+25	210															
			+35	210															
			+65	120															
	★GH0642CA2H	640	-40	150	200	60	235	2.5	1.15	641	8	16.5	—	9					
			+25	220															
			+40	220															
			+85	85															
	★GH0652CA2G	650	-40	115	200	55	220	2.6	1.2	650	8	12.5	—	9					
			-20	150															
			+25	220															
+55			220																
+90			110																

<Laser Diodes for LiDAR>

(Tc = 25°C)

Package	Model No.	Wavelength (band) λ_p (nm)	Absolute maximum ratings*1		Characteristics								Built-in monitor PD	Terminal connections	Remarks
			Po (mW)	Top (°C)	Po (mW)	Ith (mA)	Iop (mA)	Vop (V)	η_d (mW/mA)	λ_p (nm)	$\theta_{//}^{*2}$ (°)	$\theta_{\perp}^{*2}$ (°)			
② ϕ 5.6mm Can	★GH09W30A2G	905	Pulse 40W	-40 to +85	Pulse 30W	700	30A	11	1.14	905	15	20	—	8	
	★GH09W90A2G		Pulse 120W		Pulse 90W	400		11.5	3.38		7.5	28			
	★GH09W90B2G	940	Pulse 100W	-40 to +85	Pulse 90W	700	30A	15	3.14	940	8	25	—	8	

*1 The absolute maximum ratings are the limits that are not to be exceeded under any condition whatsoever, whether in testing or in actual use.

*2 Full angle of 50% peak intensity.

Note: Please inquire about combinations of packages and characteristics other than the above.

Notice

In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc.

Except where specially indicated, models listed on this page comply with the EU RoHS Directive*. For details, please contact SHARP.

*EU RoHS Directive: EU legislation restricting the use of lead, cadmium, hexavalent chromium, mercury, specific brominated flame retardants (PBB and PBDE), and phthalates (DEHP, BBP, DBP, DIBP).

Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

<Laser Diodes>

(Tc = 25°C)

Package	Model No.	Wavelength (band) λp (nm)	Absolute maximum ratings ¹		Characteristics								Built-in monitor PD	Terminal connections	Applications	
			Po (mW)	Top (°C)	Po (mW)	Ith (mA)	Iop (mA)	Vop (V)	ηd (mW/mA)	λp (nm)	θ// ² (°)	θ⊥ ² (°)				
② ϕ5.6mm Can	GH0401FA2G	405	155	−10 to +75	150	40	130	5	1.7	405	9	19	—	8	Sensor, etc.	
	GH0401FA2K												○	4		
	GH04W10A2GC		350	0 to +50	300	140	325	4.5	1.8	406	14 ^{*3}	41 ^{*3}	—	9		
	★GH0406AA2G	450	(tbd)	0 to +30	600	120	430	4.4	2	405	14 ^{*3}	38 ^{*3}	—	9	Sensor, etc.	
	GH04580A2G		85	−10 to +70	80	22	84	5.1	1.3	450	10	24	—	8		
	GH04C01A2G		1 650	−10 to +50	1 600	200	1 200	5	1.5		6.5	23	—	9		
	GH04850B2G	487	55	−10 to +60	50	40	105	6	0.8	487	8	23	—	8	Sensor, etc.	
	GH05030D2L	505	35	−10 to +60	30	30	75	6	0.65	505	8	23	—	12		
	GH05130G2K	515	35	−10 to +60	30	30	85	6.5	0.55	515	7.5	22	○	4		
	☆GH05230H2K	520	35	−10 to +60	30	25	70	6.5	0.65	520	7	22	○	4	Display, etc.	
	GH05280E2K		85		80	65	180					0.7				23
	☆GH0521DE2G		135		130	70	270					6.7				0.65
	GH06315A1K	635	16	−10 to +50	15	18	45	2.4	0.6	635	8	38	○	4	Display, etc.	
	GH06330A2G	638	30	−10 to +60	30	30	50	2.3	1.4	638	7	16	—	8		
	GH0631IA2GC		185		180	70	215	2.55	1.15		8	13		9		
	★GH0632BA2GC		210		200	55	230	2.65				15		9		
	GH0637AA2G	700	−10 to +40	700	110	810	2.46	1	638	16	35	Sensor, etc.				
	★GH0652CA2GC	650	220	−10 to +70	200	55	220	2.6	1.2	650	8		12.5	—		9
	★GH06610A2KC	660	12	−40 to +90	10	15	24	2.2	1.1	660	12		33	○		4
	GH06P25A1C		100	−10 to +70	95	40	122	2.4		661	10		16	—		3
	GH06P25A2CC									660		15.5				
	☆GH07P28F1C	785	150	−10 to +70	100	35	135	2.4	1	784	8	16	—	3		
	GH0832BA1K	830	210	−10 to +70	200	35	215	2.1	1.1	830	9	18	○	4	Sensor, etc.	
	☆GH0832FA2G		260		250	45	255	2.2	1.15		8	15	—	8		
	☆GH0852WA2G		850	700	−10 to +70	700	275	975	1.8	1	850	17	45	—		8
	☆GH0942FA2G	940	260	−10 to +70	250	(tbd)	(tbd)	(tbd)	(tbd)	940	(tbd)	(tbd)	—	8	Sensor, etc.	
	☆GH0942WA2G		700		700	315	800	1.8	1		10	35				
	③ ϕ3.8mm Can		GH04590A5G	450	95	−10 to +50	90	28	100	5.2	1.3	450	9	24		—
GH05290A5G		520	95	−10 to +50	90	60	185	6.75	0.7	520	8	23	—	8		
GH0521DE5G			135		130	70	270	6.7	0.65			22				
GH0631CA5GC		638	120	−10 to +60	120	50	150	2.5	1.2	638	8	15	—	8		
GH0631IA5G			185		150	60	190				7.5					
④ ϕ3.3mm Can	GH06510F4A	660	10	−10 to +70	7	17	26	2.2	0.85	660	13	28	○	1	Sensor, etc.	
	★GH06610A4A		12	−10 to +80	10	15	24	2.2	(tbd)		12	33	○	13		
	GH07P28F4C	785	150	−10 to +70	100	35	135	2.4	1	784	8	16	—	3		
⑤ t1.8mm Frame	GH1631AA8C	638	100	−10 to +60	100	50	130	2.45	1.2	638	8	15	—	6	Display, etc.	
	GH16P32B8C	660	100	−10 to +70	90	42	120	2.3	1.16	661	9.3	15	—	6		

*1 The absolute maximum ratings are the limits that are not to be exceeded under any condition whatsoever, whether in testing or in actual use.

*2 Full angle of 50% peak intensity.

*3 Full angle of 1/e² peak intensity.

Note: Please inquire about combinations of packages and characteristics other than the above.


Notice

In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc.

Except where specially indicated, models listed on this page comply with the EU RoHS Directive*. For details, please contact SHARP.
*EU RoHS Directive: EU legislation restricting the use of lead, cadmium, hexavalent chromium, mercury, specific brominated flame retardants (PBB and PBDE), and phthalates (DEHP, BBP, DBP, DIBP).

Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

◆Terminal Connections



<Laser diode chips>

(T_c = 25°C)

Form	Model No.	Wavelength (band) λ_p (nm)	Emitter size E _w (μm)	Light output P _o (W)	Applications
Laser chip	★GC5GW1080Z	808	190	10	
	★GC5GW1088Z	880	350	10	
	★GC5GW1091Z	915	96	10	
	★GC5GW1591Z		190	15	
	★GC5GW1094Z	940	96	10	
	★GC5GW1594Z		190	15	
	★GC5GW1097Z	976	96	10	
	★GC5GW1597Z		190	15	
	★GC5GW03F5Z	1 550	96	3	

Notice

In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc.

Except where specially indicated, models listed on this page comply with the EU RoHS Directive*. For details, please contact SHARP.

*EU RoHS Directive: EU legislation restricting the use of lead, cadmium, hexavalent chromium, mercury, specific brominated flame retardants (PBB and PBDE), and phthalates (DEHP, BBP, DBP, DIBP).

Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.