





PRODUCT NUMBER	PITCH
NAxxB1x000J0G	2.50 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



Material:

- Item①Terminal lever: Thermoplastic (UL94 V-0)
- Item②Terminal body: Thermoplastic (UL94 V-0)
- Item③Solder pin: Brass Tin plated
- Item④Wire guard: Stainless steel
- Item⑤Terminal cover: Thermoplastic (UL94 V-0)

Electrical cULus

- Voltage rating: 150V
- Current rating: 3A
- Wire range: 0.08-0.52mm²
- Solid wire(AWG): 20-28
- Stranded wire(AWG): 20-28
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

PART NO.: NA xx B1 x 0 00J0 G

N=Number of poles
Dim A=Nx2.5+1.5
Dim B=(N-1)x2.5

Poles	Tolerance
2-6p	±0.20
7-12p	±0.25
13-24p	±0.30

End stackable	No. of poles	Color	RoHS compliant
0	2	Black (RAL9005)	(lead<4%)
02	2 poles	Red (RAL3001/D)	In copper Alloy
03	3 poles	Orange(RAL2011/P)	
...	...	Yellow(RAL1018/A)	
24	24 poles	Green(RAL6018/T)	
		Blue (RAL5015/A)	
		Grey(RAL7004/P)	
		White(RAL1102)	
		C Multiple colors	

mat'l. code				surface	tolerance	projection	product family		
ltr ecn no dr date				ASME Y14.5	ASME Y14.5	ASME Y14.5	TERMINAL BLOCK		
				tolerances unless otherwise specified		MM	title		
				angles	flat		TERMINAL BLOCK		
				X°±1°	X.XX±0.1	scale	SPRING CLAMP,180D WIRE INLET,A TYPE		
				dr	EVIN ZHONG	052314	dwg no		
				enrg	EVIN ZHONG	052314	sheet 1 of 1 size		
				chr	HANKE FENG	052314	NAXXB1x000J0G		
				appd	SHI JUN	052314	A4		
sheet index				revision	A		type		
				sheet	1		CUSTOMER Drawing		