G9TB

AC Power Latching Relay

120 A Compact and high power latching relay

- High power switching: 120 A, 276 VAC
- Compact size: 37 mm × 43 mm × 22 mm
- Low temperature-rise
- High overcurrent capability, conforming to IEC62055-31 UC3
- Conforms to UL 508



Model Number Structure

G9TB-□1A□-E
1 2 3 4 5

1. Relay Function
   U: Single-winding latching
   K: Double-winding latching
2. Number of poles
   1: 1-Pole
3. Contact Form
   A: SPST-NO
4. Terminal shape
   TH: M8 securing screw
   TW: Welding terminals
5. Classification
   E: High capacity

Application Examples

- Smart Meter
- Lighting control
- PV Inverter
- EV Charger

Ordering Information

Classification	Contact Form	Terminal Shape	Enclosure rating	Model	Rated coil voltage	Minimum packing unit
Single coil	SPST-NO	M8 securing screw	Dust protection	G9TB-U1ATH-E	12 VDC	25 pcs/tray
		Welding terminals		G9TB-U1ATW-E		
Double coils		M8 securing screw		G9TB-K1ATH-E	12 VDC	
		Welding terminals		G9TB-K1ATW-E		

Note. When ordering, add the rated coil voltage to the model number.
Example: G9TB-U1ATH-E DC12
└Rated coil voltage
However, the notation of the coil voltage on the product case as well as on the packing will be marked as[][] VDC.

Ratings

● Coil

Single-winding Latching Type

Item / Rated Voltage	(V)	Rated current (mA)	Coil resistance (Ω)	Must set voltage	Must reset voltage	Max. voltage	Power consumption	
				% of rated voltage			Set coil (W)	Reset coil (W)
DC	12	225	53.3	80% max.	80% max.	110% max.	Approx. 2.7	

Double-winding Latching Type

Item / Rated Voltage	(V)	Rated current (mA)		Coil resistance (Ω)		Must set voltage	Must reset voltage	Max. voltage	Power consumption	
		Set coil	Reset coil	Set coil	Reset coil	% of rated voltage			Set coil (W)	Reset coil (W)
DC	12	451	451	26.6	26.6	80% max.	80% max.	110% max.	Approx. 5.4	Approx. 5.4

Note 1. The rated current and coil resistance were measured at a coil temperature of 23°C with tolerances of ± 10%.
Note 2. The operating characteristics are measured at a coil temperature of 23°C.
Note 3. The maximum permissible voltage is the maximum value of the fluctuation range for the Relay coil operating power supply and was measured at an ambient temperature of 23°C.

● Contacts

Item / Model / Load	G9TB-U1A□-E/G9TB-K1A□-E	
	Resistive load	Inductive load (PF=0.5)
Contact type	SPST-NO	
Contact material	Ag Alloy	
Rated load	120 A at 276 VAC	100 A at 276 VAC
Rated carry current	120 A	
Max. switching voltage	276 VAC	
Max. switching current	120 A	100 A

Downloaded from Arrow.com.

Characteristics

Item		G9TB-U1A□ -E	G9TB-K1A□ -E
Contact resistance *1		0.4 mΩ max.	
Set time *2		25 ms max.	20 ms max.
Reset time *2		25 ms max.	20 ms max.
Minimum pulse width		100 ms	
Maximum pulse width		1,000 ms	
Insulation resistance *3		1,000 MΩ min.	
Dielectric strength	Between coil and contacts	4,000 VAC, 50/60 Hz for 1 min	
	Between contacts of the same polarity	2,000 VAC, 50/60 Hz for 1 min	
Impulse withstand voltage	Between coil and contacts	8 kV	
Vibration resistance	Destruction	10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)	
	Malfunction	10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)	
Shock resistance	Destruction	1,000 m/s^2	
	Malfunction	100 m/s^2	
Durability	Mechanical	100,000 operations min. (at 7,200 operations/h)	
	Electrical *4	10,000 operations typical, resistive load 120 A, 276 VAC (operation: ON for 10 sec, OFF for 20 sec)	
		5,000 operations, resistive load 100 A, 276 VAC and then 5,000 operations, inductive load (PF=0.5) 100 A, 276 VAC (operation: ON for 10 sec, OFF for 20 sec) *5	
Ambient operating temperature		-40 to 85°C (with no icing or condensation)	
Ambient operating humidity		5 to 85%	
Weight		Approx. 70 g	


Note. The values given above are initial values.
*1. Measurement conditions: 24 VDC, 1 A, voltage drop method.
*2. Measurement conditions: Rated operating voltage applied, not including contact bounce.
Ambient temperature: 23°C
*3. Measurement conditions: The insulation resistance was measured with a 500 VDC megohm meter at the same locations as the dielectric strength was measured.
*4. Contact your OMRON sales representative for Electrical Durability technical data.
*5. The characteristic meets IEC62055-31 test requirement.


Downloaded from Arrow.com.

Dimensions


(Unit: mm)

G9TB-U1ATH-E







Terminal arrangement/Internal Connections
(TOP VIEW)




Check carefully the coil polarity of the Relay.

G9TB-U1ATW-E







Terminal arrangement/Internal Connections
(TOP VIEW)




Check carefully the coil polarity of the Relay.

G9TB-K1ATH-E






Terminal arrangement/Internal Connections
(TOP VIEW)




Check carefully the coil polarity of the Relay.


Downloaded from Arrow.com.

G9TB-K1ATW-E





Terminal arrangement/Internal Connections
(TOP VIEW)




Check carefully the coil polarity of the Relay.


Note 1. Relay is delivered as "set" status unless specified otherwise. However, the status may change due to the shock from transportation or mounting operations. Therefore, it is recommended the relay should be set to the expected status via a power supply before being used.
Note 2. In order to maintain "set" or "reset" status, the energizing voltage to coil & the pulse width shouldn't lower then the rated value.
Note 3. Do not energize both of set and reset coil simultaneously.
Note 4. Energizing time longer than 1,000 ms should be avoided.

Engineering Data

● **Maximum Switching Capacity**

G9TB-U1A□ -E
G9TB-K1A□ -E





Approved Standards

The approval rating values for overseas standards are different from the performance values determined individually. Confirm the values before use.

● **UL/C-UL Certificated: (File No. E41515)**

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G9TB-U1ATH-E G9TB-U1ATW-E G9TB-K1ATW-E G9TB-K1ATH-E	SPST-NO (1a)	12V DC	120 A, 277 V AC (Resistive) 70°C	6,000
			100 A, 277 V AC (Resistive) and then 100 A, 277 V (PF=0.5), 10 sec. ON / 20 sec. OFF, 40°C	5,000 for resistive and then 5,000 for PF=0.5

Downloaded from Arrow.com.

Safety Precautions

• Please refer to "PCB Relays Common Precautions" for correct use.

Correct Use

● Installation

- The relay contacts are polarized. Incorrect wiring may cause a failure to break the circuit. Wire the Relay with care.
- Install the Relays in locations that are as dry as possible and have as little dust, dirt, and harmful gas.
- Using the Relay under high temperature, high humidity, or harmful gas may deteriorate its performance characteristics due to condensation or corrosive materials, resulting in failure or burn damage to the Relay.

● Relay Service Life

- The electrical durability of these Relays is specified as the number of load switching operations under a resistive load and OMRON-specified standard testing conditions.
  The coil drive circuit, ambient environment, switching frequency, or load conditions (e.g., inductive load or capacitor load) may reduce the service life and possibly lead to failure to break. Always confirm the service life in the actual equipment.

● Wiring

- Be sure to tighten all screws to the appropriate torque given below.
- Loose screws may result in burning due to abnormal heat generation during energization.
- M8 screws : 8.82 to 9.80 N·m
- Use a spring washer in order to prevent deformation and it from loosening.
- Allow suitable slack on leads when wiring, and do not apply excessive force to the terminals.

Please check each region's Terms & Conditions by region website.

OMRON Corporation
Device & Module Solutions Company

Regional Contact

Americas
https://components.omron.com/us
Europe
https://components.omron.com/eu
Asia-Pacific
https://components.omron.com/ap
China
https://components.omron.com.cn
Korea
https://components.omron.com/kr
Japan
https://components.omron.com/jp

© OMRON Corporation 2018-2024 All Rights Reserved.
In the interest of product improvement, specifications are subject to change without notice.

Cat. No. J221-E1-05
0924 (0318)

Downloaded from Arrow.com.