





	1	2	3	4	5	6	7	
A								A
B								B
C								C
D								D
E								E
F								F
G								G
H								H
	1	2	3	4	5	6	7	SVxxx



N=NUMBER OF CONTACTS

P.C.B LAYOUT



Material

- Terminal body (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating "-" slot type
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0),Blue

Electrical cULus/CSA/VDE

- Voltage rating: 300VAC/250VAC/250VAC
- Current rating: 15A/16A/17.5A
- Wire range:0.75-1.5mm²
- Solid wire(AWG): 14-22/14-22
- Stranded wire(AWG): 14-22/14-22
- Torque: 2.6Lb-In/4Kgf.cm/0.4Nm
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV/1.5KV/2KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- SAFETY APPROVAL :

RoHS compliant

Scale	1:1						Date	Name	Customer-No.	
TOLERANCE						Drawn	29.07.2009	Dean		
X.	±0.50					Approved	29.07.2009	Hellwig	ASSMANN WSW-No. A-TB500-TCxx	
X.X	±0.30									
X.XX	±0.10									
DIM	TOL								Drawing-No.	
X.°	±1°								ASS 3591 CO	rev01
X.X°	±X°	①	Drawn	29.07.2009	Dean				Replace	Sheet
Angle	TOL	Id.	Modification	Date	Name					