Part Number : 349674004
Product Description : Mini50 Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option D, Stone Gray
Series Number : 34967
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

349674004_sd.pdf

PK-31301-898-000.pdf

PK-31301-898-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

348940001-AS-CH-000.pdf

AS-34894-0001-001.pdf

AS-34894-0001-001.pdf

349670001-000.pdf

349670001-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains

Downloaded from Arrow.com.

	Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	34967
Description	Mini50 Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option D, Stone Gray
Application	Automotive, Power, Sealed, Wire-to-Board
Comments	-40°C to +105°C operating temperature for tin terminals; -40°C to +125°C operating temperature for silver terminals
Product Name	Mini50 Sealed
UPC	887191620411

Downloaded from Arrow.com.

Physical

Circuits (maximum)	4
Color - Resin	Black, Stone Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	3.300/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarization	D
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Molex does not manufacture the mating header interface. To provide you with maximum design flexibility, we include the interface specification drawing with the part drawing, and a 3D model is available at the following URL so that you may design the interface into your device as you require: COMING SOON

Use with Part(s)

Description	Part Number
CTX50 Sealed Receptacle	34905

Downloaded from Arrow.com.

Terminals	

Downloaded from Arrow.com.