Part Number : 1210360799
Product Description : Brad mPm DIN Form A-18mm to Micro-Change (M12) 5 Pole Cordset, S0 Circuit, Yellow LED, Male (90°) to Male (Straight), 0.50mm² Black PUR Cable, 2.0m (6.56') Length, 110V
Series Number : 121036
Status : Obsolete
Product Category : Industrial Cable Assemblies
Engineering Part Number : E850C0P12M020



Obsolete

Documents and Resources

Drawings

1210360799_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Industrial Cable Assemblies
Series	121036
Description	Brad mPm DIN Form A-18mm to Micro-Change (M12) 5 Pole Cordset, S0 Circuit, Yellow LED, Male (90°) to Male (Straight), 0.50mm² Black PUR Cable, 2.0m (6.56') Length, 110V
IP Rating	IP65
Product Name	Micro-Change (M12),mPm
Protocol	N/A
Type	Double Ended
UPC	78172534571

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	110V

Physical

Cable Diameter	5.50mm (.216")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Brad mPm DIN A - 18mm
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Male-Male
Keyway	Single
LED Indicator	Yellow
Material - Cable Jacket	PUR
Material - Connector Body	Polypropylene
Material - Contact	Copper Alloy

Obsolete

Downloaded from Arrow.com.

Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	130.713/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +75°C
Wire/Cable Type	PUR
Wire Size (AWG)	20

Obsolete

Downloaded from Arrow.com.