

PLC-BSC-230UC/21-21 - Relay base

2967044

<https://www.phoenixcontact.com/us/products/2967044>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

14 mm PLC basic terminal block with screw connection, without relay or solid-state relay, for mounting on DIN rail NS 35/7,5, 2 changeover contacts, input voltage 230 V AC/DC



Commercial data

Item number	2967044
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C461
Product key	CK6232
GTIN	4017918156480
Weight per piece (including packing)	63.9 g
Weight per piece (excluding packing)	55.82 g
Customs tariff number	85366990
Country of origin	DE

PLC-BSC-230UC/21-21 - Relay base

2967044

<https://www.phoenixcontact.com/us/products/2967044>



Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Relay socket
Product family	PLC-INTERFACE
Application	Universal
Operating mode	100% operating factor
Compatible components	Miniature relay, REL-MR-110DC/21-21AU, REL-MR-110DC/21-21

Data management status

Article revision	12
------------------	----

Insulation characteristics

Pollution degree	3
------------------	---

Input data

Nominal input voltage U_N	230 V AC/DC
Protective circuit	Bridge rectifier
Nominal input voltage U_N	230 V AC/DC

Output data

Compatible components	Miniature relay, REL-MR-110DC/21-21AU, REL-MR-110DC/21-21
-----------------------	---

Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ² 0.2 mm ² ... 2.5 mm ² (Single ferrule) 2x 0.5 mm ² ... 1.5 mm ² (TWIN ferrule)
Conductor cross section AWG	26 ... 14
Tightening torque	0.6 Nm ... 0.8 Nm

PLC-BSC-230UC/21-21 - Relay base

2967044

<https://www.phoenixcontact.com/us/products/2967044>



Signaling

Status display	LED
----------------	-----

Dimensions

Width	14 mm
Height	80 mm
Depth	94 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0 (Housing)

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Approvals

CE	
Certificate	CE-compliant

UKCA	
Certificate	UKCA-compliant

Shipbuilding approval	
Certificate	TAE0000196

Corrosive gas test	
Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

DNV GL data	
Temperature	D
Humidity	A
Vibration	B/C
EMC	B
Enclosure	Required protection according to the Rules shall be provided upon installation on board

EMC data

Low Voltage Directive	Conformance with Low Voltage Directive
Electromagnetic compatibility	Conformance with EMC directive

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

PLC-BSC-230UC/21-21 - Relay base

2967044

<https://www.phoenixcontact.com/us/products/2967044>



Assembly note	in rows with zero spacing
Mounting position	any

PLC-BSC-230UC/21-21 - Relay base

2967044

<https://www.phoenixcontact.com/us/products/2967044>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2967044>



cUL Recognized

Approval ID: E238705



UL Recognized

Approval ID: E238705



EAC

Approval ID: RU D-DE.B*00573/18



DNV GL

Approval ID: TAE0000196

cULus Recognized

PLC-BSC-230UC/21-21 - Relay base

2967044

<https://www.phoenixcontact.com/us/products/2967044>



Classifications

ECLASS

ECLASS-11.0	27371603
ECLASS-12.0	27371603
ECLASS-13.0	27371603

ETIM

ETIM 9.0	EC001456
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	45e1df6d-94c9-43ab-af5d-674f3819ed7b

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com