






- NOTES:
- 1. MATERIAL:
CONTACTS: COPPER ALLOY
SHELL: COPPER ALLOY
HOUSING: UL 94V-0 RATED, HIGHT TEMPERATURE THERMOPLASTIC;
 - 2. PLATING:
CONTACTS: SEE PRODUCT NUMBER CODE
SHELL: SEE PRODUCT NUMBER CODE;
 - 3. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER;
 - 4. RECOMMENDED PC BOARD THICKNESS OF 1.57mm
 - 5. 2.67mm MAXIMUM PANEL THICKNESS IF MOUNTED BEHIND PANEL;
 - 6. PRODUCT SPEC GS-12-095
 - 7. PACKING STANDARD GS-14-920, WILL BE APPLIED FOR LEAD FREE P/N'S;
 - 8. THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008;
 - 9. THE HOUSING WILL WITHSTAND EXPOSURE TO 260~C PEAK
TERMERATURE FOR 20 SECONDS IN A CONVECTION, INFRO-RED
OR VAPOR PHASE REFLOW OVEN;
 - 10. HOUSING PULL OFF THE SHELL RETENTION FORCE: 250N MIN;
 - 11. THE PRODUCT CAN BE USED PIP PROCESS;
 - 12. THE PRODUCT CAN PASS 16 HOURS SALT SPRAY TEST.



spec ref	dr	Li-Qing Lei	2014/04/21	projection	MM	size	A3	scale	5.000
tolerance std	eng	Li-Qing Lei	2019/06/03	chr	-	ecn no	ELX-N-33759-1	rel level	Released
	appr	Tim Yao	2019/06/03	product family		rel level	Released		
surface	linear	0.X	±0.3	Amphenol FCi	title	USB RECECPTACLE	dwg no	10129475	rev
		0.XX	±0.2			R/A, T/H, A TYPE			B
		0.XXX	±0.1	www.fci.com	cat. no.		Product - Customer Drw	sheet 1 of 2	
	angular	0°	±3°						

A

B

C



D

A

B

C

D



PRODUCT NUMBER DESCRIPTION

10129475- X X X X X X LF

BASE PRODUCT NUMBER

HOUSING COLOR

0 - BLACK
1 - WHITE

SHELL TYPE AND SHELL PLATING OPTIONS

1 - NO BACK SHIELD, NICKEL PLATING ONLY

EXTENSION

0 - NONE

TERMINAL PLATING OPTION

0 - 1.25µm Ni UNDERPLATE
0.76µm GXT CONTACT AREA
2.50µm MATTE TIN TAIL AREA FOR P/N'S


PACKAGING OPTIONS

A - TAPE AND REEL
B - TUBES
T - TRAY

DATE CODE

P - PRINT DATECODE
N - WHITHOUT DATECODE

LEAD FREE

spec ref				dr	Li-Qing Lei	2014/04/21	projection 	MM 	size	A3	scale	5.000	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Li-Qing Lei	2019/06/03			ecn no				ELX-N-33759-1
				chr	-	-			rel level				Released
				appr	Tim Yao	2019/06/03			product family				
surface ✓	linear	0.X	±0.3	Amphenol FCi	title USB RECECPTACLE R/A, T/H, A TYPE				dwg no	10129475		rev B	
		0.XX	±0.2										
		0.XXX	±0.1										
	angular	0°	±3°		cat. no.				Product - Customer Drw		sheet 2 of 2		