2.5 V / 3.3 V Differential 4:1 Mux Input to 1:2 LVPECL Clock/Data Fanout / Translator

Multi−Level Inputs w/ Internal Termination

NB7L572

The NB7L572 is a high performance differential 4:1 Clock/Data input multiplexer and a 1:2 LVPECL Clock/Data fanout buffer. The INx/$\overline{\text{INx}}$ inputs includes internal 50 Ω termination resistors and will accept differential LVPECL, CML, or LVDS logic levels. The NB7L572 incorporates a pair of Select pins that will choose one of four differential inputs and will produce two identical LVPECL output copies of Clock or Data operating up to 7 GHz or 10 Gb/s, respectively. As such, NB7L572 is ideal for SONET, GigE, Fiber Channel, Backplane and other Clock/Data distribution applications.


The NB7L572 INx/$\overline{\text{INx}}$ inputs, outputs and core logic are powered by a 2.5 V ±5% V or 3.3 V ±10% power supply. The two differential LVPECL outputs will swing 750 mV when externally terminated with a 50 Ω resistor to V_{CC} − 2 V, and are optimized for low skew and minimal jitter.

The NB7L572 is offered in a low profile 5x5 mm 32-pin QFN Pb-free package. Application notes, models, and support documentation are available at www.onsemi.com.

The NB7L572 is a member of the GigaComm™ family of high performance clock products.


Features

- Input Data Rate > 10.7 Gb/s Typical
- Data Dependent Jitter < 15 ps
- Maximum Input Clock Frequency > 7 GHz Typical
- Random Clock Jitter < 0.8 ps RMS
- Low Skew 1:2 LVPECL Outputs, < 15 ps max
- 4:1 Multi−Level Mux Inputs, Accepts LVPECL, CML LVDS
- 150 ps Typical Propagation Delay
- 45 ps Typical Rise and Fall Times
- Differential LVPECL Outputs, 750 mV Peak-to-Peak, Typical
- Operating Range: V_{CC} = 2.375 V to 3.6 V
- Internal 50 Ω Input Termination Resistors
- V_{REFAC} Reference Output
- −40°C to +85°C Ambient Operating Temperature
- These are Pb−Free Devices




QFN32
MN SUFFIX
CASE 488AM

MARKING DIAGRAM*



A	= Assembly Site
WL	= Wafer Lot
YY	= Year
WW	= Work Week
G	= Pb−Free Package

*For additional marking information, refer to Application Note AND8002/D.



ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 10 of this data sheet.

© Semiconductor Components Industries, LLC, 2012

Downloaded from Arrow.com.




Figure 1. Pinout Configuration (Top View)

Table 1. INPUT SELECT FUNCTION TABLE

SEL1*	SEL0*	Clock / Data Input Selected
0	0	IN0 Input Selected
0	1	IN1 Input Selected
1	0	IN2 Input Selected
1	1	IN3 Input Selected

*Defaults HIGH when left open.

Downloaded from Arrow.com.

Table 2. PIN DESCRIPTION

Pin	Name	I/O	Description
1, 4 5, 8 25, 28 29, 32	IN0, $\overline{IN0}$ IN1, $\overline{IN1}$ IN2, $\overline{IN2}$ IN3, $\overline{IN3}$	LVPECL, CML, LVDS Input	Non−inverted, Inverted, Differential Clock or Data Inputs.
2, 6 26, 30	VT0, VT1 VT2, VT3		Internal 100 Ω Center−tapped Termination Pin for INx / $\overline{INx}$
15 18	SEL0 SEL1	LVTTL/LVCMOS Input	Input Select pins, default HIGH when left open through a 28k−Ω pull−up resistor. Input logic threshold is V_{CC}/2. See Select Function, Table 1.
14, 19	NC	−	No Connect
10, 13, 16 17, 20, 23	VCC	−	Positive Supply Voltage. All V_{CC} pins must be connected to the positive power supply for correct DC and AC operation.
11, 12 21, 22	$\overline{Q0}$, Q0 $\overline{Q1}$, Q1	LVPECL Output	Inverted, Non−inverted Differential Outputs.
9, 24	GND		Negative Supply Voltage, connected to Ground
3 7 27 31	VREFAC0 VREFAC1 VREFAC2 VREFAC3	−	Output Voltage Reference for Capacitor−Coupled Inputs
−	EP	−	The Exposed Pad (EP) on the QFN−32 package bottom is thermally connected to the die for improved heat transfer out of package. The exposed pad must be attached to a heat−sinking conduit. The pad is electrically connected to the die, and must be electrically connected to GND.

1. In the differential configuration when the input termination pins (VT0, VT1, VT2, VT3) are connected to a common termination voltage or left open, and if no signal is applied on INx / $\overline{INx}$ input, then the device will be susceptible to self−oscillation.
2. All VCC, and GND pins must be externally connected to a power supply for proper operation.

Downloaded from Arrow.com.

Table 3. ATTRIBUTES

Characteristic		Value
ESD Protection	Human Body Model Machine Model	> 4 kV > 150 V
Input Pullup Resistor (R_{PU})		28 kΩ
Moisture Sensitivity (Note 3)	QFN32	Level 1
Flammability Rating Oxygen Index: 28 to 34		UL 94 V−0 @ 0.125 in
Transistor Count		205
Meets or exceeds JEDEC Spec EIA/JESD78 IC Latchup Test		

3. For additional information, see Application Note AND8003/D.

Table 4. MAXIMUM RATINGS

Symbol	Parameter	Condition 1	Condition 2	Rating	Unit
V_{CC}	Positive Power Supply	GND = 0 V		−0.5 to +4.0	V
V_{IN}	Positive Input Voltage	GND = 0 V		−0.5 to V_{CC} +0.5	V
V_{INPP}	Differential Input Voltage |IN − $\overline{IN}$|			1.89	V
I_{out}	LVPECL Output Current	Continuous Surge		50 100	mA mA
I_{IN}	Input Current Through RT (50 Ω Resistor)			±40	mA
T_A	Operating Temperature Range			−40 to +85	°C
T_{stg}	Storage Temperature Range			−65 to +150	°C
θ_{JA}	Thermal Resistance (Junction−to−Ambient) (Note 4)	0 lfpm 500 lfpm	QFN−32 QFN−32	31 27	°C/W °C/W
θ_{JC}	Thermal Resistance (Junction−to−Case) (Note 4)		QFN−32	12	°C/W
T_{sol}	Wave Solder	≤ 20 sec		265	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

4. JEDEC standard multilayer board − 2S2P (2 signal, 2 power) with 8 filled thermal vias under exposed pad.

Downloaded from Arrow.com.

Table 5. DC CHARACTERISTICS POSITIVE LVPECL OUTPUT V_{CC} = 2.375 V to 3.6 V, GND = 0 V, TA = −40°C to +85°C (Note 6)

Symbol	Characteristic	Min	Typ	Max	Unit
POWER SUPPLY					
V_{CC}	Power Supply Voltage V_{CC} = 2.5V V_{CC} = 3.3 V	2.375 3.0	2.5 3.3	2.625 3.6	V
I_{CC}	Power Supply Current for V_{CC} (Inputs and Outputs Open)		90	110	mA
LVPECL OUTPUTS					
V_{OH}	Output HIGH Voltage (Note 6) V_{CC} = 2.5 V V_{CC} = 3.3 V	V_{CC} − 1145 1355 2155	V_{CC} − 900 1600 2400	V_{CC} − 825 1675 2475	mV
V_{OL}	Output LOW Voltage (Note 6) V_{CC} = 2.5 V V_{CC} = 3.3 V	V_{CC} − 2000 500 1300	V_{CC} − 1700 800 1600	V_{CC} − 1500 1000 1800	mV
DIFFERENTIAL CLOCK INPUTS DRIVEN SINGLE−ENDED (Figures 4 & 6) (Note 7)					
V_{IH}	Single−Ended Input HIGH Voltage	V_{th} + 100		V_{CC}	mV
V_{IL}	Single−Ended Input LOW Voltage	GND		V_{th} − 100	mV
V_{th}	Input Threshold Reference Voltage Range (Note 8)	1100		V_{CC} − 100	mV
V_{ISE}	Single−Ended Input Voltage (V_{IH} − V_{IL})	200		2400	mV
VREFAC					
V_{REF-AC}	Output Reference Voltage (100 μA Load)	V_{CC} − 1500	V_{CC} − 1200	V_{CC} − 1000	mV
DIFFERENTIAL INPUTS DRIVEN DIFFERENTIALLY (Figures 5 & 7) (Note 9)					
V_{IHD}	Differential Input HIGH Voltage (IN, $\overline{IN}$)	1200		V_{CC}	mV
V_{ILD}	Differential Input LOW Voltage (IN, $\overline{IN}$)	0		V_{IHD} − 100	mV
V_{ID}	Differential Input Voltage (IN, $\overline{IN}$) (V_{IHD} − V_{ILD})	100		1200	mV
V_{CMR}	Input Common Mode Range (Differential Configuration, Note 10) (Figure 8)	800		V_{CC} − 50	mV
I_{IH}	Input HIGH Current IN/$\overline{IN}$ (VT IN/VT $\overline{IN}$ Open)	−150		150	μA
I_{IL}	Input LOW Current IN/$\overline{IN}$ (VT IN/VT $\overline{IN}$ Open)	−150		150	μA
CONTROL INPUT (SELx Pin)					
V_{IH}	Input HIGH Voltage for Control Pin	2.0		V_{CC}	V
V_{IL}	Input LOW Voltage for Control Pin	GND		0.8	V
I_{IH}	Input HIGH Current			40	μA
I_{IL}	Input LOW Current	−215		0	μA
TERMINATION RESISTORS					
R_{TIN}	Internal Input Termination Resistor (Measured from INx to VTx)	45	50	55	Ω

NOTE: Device will meet the specifications after thermal equilibrium has been established when mounted in a test socket or printed circuit board with maintained transverse airflow greater than 500 lfpm.

5. Input and Output parameters vary 1:1 with V_{CC}.
6. LVPECL outputs loaded with 50 Ω to V_{CC} − 2V for proper operation.
7. Vth, V_{IH}, $V_{IL,}$, and V_{ISE} parameters must be complied with simultaneously.
8. Vth is applied to the complementary input when operating in single−ended mode.
9. V_{IHD}, $V_{ILD,}$ V_{ID} and V_{CMR} parameters must be complied with simultaneously.
10. V_{CMR} min varies 1:1 with GND, V_{CMR} max varies 1:1 with V_{CC}. The V_{CMR} range is referenced to the most positive side of the differential input signal.

Downloaded from Arrow.com.

Table 6. AC CHARACTERISTICS V_{CC} = 2.375 V to 3.6 V, GND = 0 V, TA = −40°C to +85°C (Note 11)

Symbol	Characteristic		Min	Typ	Max	Unit
f_{MAX}	Maximum Input Clock Frequency $V_{OUT} \geq$ 400 mV		7	8		GHz
$f_{DATAMAX}$	Maximum Operating Data Rate NRZ, (PRBS23)		10	11		Gbps
V_{OUTPP}	Output Voltage Amplitude (@ $V_{INPPmin}$) (Figure 2 & 9) (Note 12)	$f_{in} \leq$ 5 GHz $f_{in} \leq$ 7 GHz	550 400	750 500		mV
t_{PLH}, t_{PHL}	Propagation Delay to Differential Outputs Measured at Differential Cross−Point	@ 1 GHz INx/$\overline{INx}$ to Qx/$\overline{Qx}$ (Figure 9) @ 50 MHz SELx to Qx (Figure 10)	125 300	150	175 1000	ps
$t_{PD\ Tempco}$	Differential Propagation Delay Temperature Coefficient			115		fs/°C
t_{skew}	Output − Output skew (within device) (Note 13) Device − Device skew (tpd max − tpd min)			0	10 50	ps
t_{DC}	Output Clock Duty Cycle (Reference Duty Cycle = 50%)		45	50	55	%
t_{JITTER}	Additive Random Clock Jitter, RJ(RMS) (Note 14) Data Dependent Jitter, DDJ (Note 15)	$f_{in} \leq$ 7.0 GHz $f_{in} \leq$ 10 Gbps		0.5 6	0.8 15	ps rms ps pk−pk
V_{INPP}	Input Voltage Swing (Differential Configuration) (Note 16)		100		1200	mV
t_r, t_f	Output Rise/Fall Times @ 1 GHz; (20% − 80%), V_{IN} = 800 mV Q, $\overline{Q}$		25	45	65	ps

NOTE: Device will meet the specifications after thermal equilibrium has been established when mounted in a test socket or printed circuit board with maintained transverse airflow greater than 500 lfpm.

11. Measured using a 100 mVpk−pk source, 50% duty cycle clock source. All output loading with external 50 Ω to V_{CC} − 2 V. Input edge rates 40 ps (20% − 80%).
12. Output voltage swing is a single−ended measurement operating in differential mode.
13. Skew is measured between outputs under identical transitions and conditions. Duty cycle skew is defined only for differential operation when the delays are measured from cross−point of the inputs to the cross−point of the outputs.
14. Additive RMS jitter with 50% duty cycle clock signal.
15. Additive Peak−to−Peak data dependent jitter with input NRZ data at K28.5.
16. Input voltage swing is a single−ended measurement operating in differential mode.




Figure 2. CLOCK Output Voltage Amplitude (V_{OUTPP}) / RMS Jitter vs. Input Frequency (f_{in}) at Ambient Temperature (typical)




Figure 3. Input Structure

Downloaded from Arrow.com.




Figure 4. Differential Input Driven Single−Ended




Figure 5. Differential Inputs Driven Differentially




Figure 6. V_{th} Diagram




Figure 7. Differential Inputs Driven Differentially




Figure 8. V_{CMR} Diagram




Figure 9. AC Reference Measurement




Figure 10. SELx to Qx Timing Diagram

Downloaded from Arrow.com.




Figure 11. Typical Termination for Output Driver and Device Evaluation (See Application Note AND8020/D – Termination of ECL Logic Devices.)

Downloaded from Arrow.com.




Figure 12. LVPECL Interface




Figure 13. LVDS Interface




Figure 14. Standard 50 Ω Load CML Interface




Figure 15. Capacitor−Coupled Differential Interface (VT Connected to V_{REFAC})

*V_{REFAC} bypassed to ground with a 0.01 μF capacitor




Figure 16. Capacitor−Coupled Single−Ended Interface (VT Connected to External V_{REFAC})

Downloaded from Arrow.com.

ORDERING INFORMATION

Device	Package	Shipping†
NB7L572MNG	QFN32 (Pb−Free)	74 Units / Tube
NB7L572MNR4G	QFN32 (Pb−Free)	1000 / Tape & Reel


†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

GigaComm is a trademark of Semiconductor Components Industries, LLC dba “**onsemi**” or its affiliates and/or subsidiaries in the United States and/or other countries.


Downloaded from Arrow.com.


QFN32 5x5, 0.5P
CASE 488AM
ISSUE A

DATE 23 OCT 2013




SCALE 2:1







DETAIL A
ALTERNATE TERMINAL CONSTRUCTIONS



DETAIL B
ALTERNATE CONSTRUCTION



SIDE VIEW




BOTTOM VIEW

NOTES:
1. DIMENSIONS AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30MM FROM THE TERMINAL TIP.
4. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

	MILLIMETERS	
DIM	MIN	MAX
A	0.80	1.00
A1	---	0.05
A3	0.20 REF	
b	0.18	0.30
D	5.00 BSC	
D2	2.95	3.25
E	5.00 BSC	
E2	2.95	3.25
e	0.50 BSC	
K	0.20	---
L	0.30	0.50
L1	---	0.15

GENERIC MARKING DIAGRAM*




XXXXX = Specific Device Code
A = Assembly Location
WL = Wafer Lot
YY = Year
WW = Work Week
▪ = Pb−Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking.
Pb−Free indicator, “G” or microdot “ ▪”, may or may not be present.

RECOMMENDED SOLDERING FOOTPRINT*



DIMENSION: MILLIMETERS

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	**98AON20032D**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**QFN32 5x5 0.5P**	**PAGE 1 OF 1**

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2005

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.