



**Part Number :** [1202440002](#)  
**Product Description :** Micro-Change (M12)  
Circular Hybrid Technology (CHT) Female  
Receptacle, Dual Keyway, M16x1.5mm Back  
Panel Mount, 8 Pole (4 Signal, 4 Power)  
**Series Number :** 120244  
**Status :** Active  
**Product Category :** Circular Industrial  
Connectors




## Documents & Resources

**Drawings**  
[1202440002\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 3; 33; 34; 39
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	120244
Description	Micro-Change (M12) Circular Hybrid Technology (CHT) Female Receptacle, Dual Keyway, M16x1.5mm Back Panel Mount, 8 Pole (4 Signal, 4 Power)
IP Rating	IP67
Product Name	CHT, Micro-Change (M12)
Type	Adapter
UPC	884982666979

### Agency

UL	E218123
----	---------

### Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	30V

### Physical

Coupling Type	External Thread
Gender	Female
Keyway	Dual
Length	N/A
Material - Component	Stainless Steel Type 303
Mounting Thread Size	M12
Net Weight	22.679/g
Orientation	Straight
Panel Mount	Back
Poles	8
Temperature Range - Operating	-25° to +75°C

Wire/Cable Type	N/A
Wire Size (AWG)	N/A

---

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Change (M12) Circular Hybrid Technology (CHT) Cordsets and Receptacles	<u>120244</u>

---

This document was generated on Apr 22, 2025