

Copyright FCI.


FCIconnect.com

PRODUCT NUMBER	PITCH
TSxx01xD00J0G	7.62 mm





SETION P-P



Material
- Item ⓐ Top body:Thermoplastic (UL94V-0)
- Item ⓑ Bottom body:Thermoplastic (UL94V-0)
- Item ⓒ Terminal screw:Steel Zinc plating "-" slot type
- Item ⓓ Clamp:Brass, Ni plated
- Item ⓔ Female contact:PhBz (CuSn) Tin plated
- Item ⓕ With flange screw:Steel Zinc plating M2.5 "+/-" combination type

Electrical cULus/TUV
- Voltage rating: 300VAC/750VAC
- Current rating: 15A/15A
- Wire range:0.2-2.5mm^2
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5 Lb-In 0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus TÜV

Dim A=(N-1)×7.62+5.6
Dim B=(N-1)×7.62
Dim C=(N-1)×7.62+12.2
Dim D=(N-1)×7.62+18.0
Dim E=(N-1)×7.62
N=Number of poles

POLES	Tolerance
2p-6p	±0.20
7p-11p	±0.30
12p-16p	±0.40

PART NO.: TS xx 01 x D 00J0 G

Solid block
No. of poles
02 2 poles
03 3 poles
... ...
16 16 poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family: TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title: TERMINAL BLOCK
				angles / linear: X.±0.5		MM	PLUGGABLE PLUG,HOOK ON BACK SIDE,WITH FLANGE
				X°±1° / X.X±0.3			
					X.XX±0.1	scale	dwg no: TSxx01xD00J0G — sheet 1 of 1 — size A4
				dr	EVIN ZHONG 041914		
				engr	EVIN ZHONG 041914		type: CUSTOMER Drawing
				chr	HANKE FENG 041914		
				appd	SHI JUN 041914		
sheet	revision	A					
index	sheet	1					

Downloaded from Arrow.com.