


REV.	CHANGE	DATE	APPD.
G	INPUT INTO ACAD ECO 13584	---	---



DIAMETER	.080 MAX
LENGTH	.180 MAX
LEAD LENGTH	1.12±.03
LEAD MATERIAL	.020 DIA. +.003,-.005. COPPER CLAD STEEL — TINNED

RESISTANCE (OHMS)

TEMP. °C	MINIMUM	NOMINAL	MAXIMUM	REF TOL
5	24130	25400	26670	±5%
25	9500.0	10000	10500	±5%
45	4152.0	4370.0	4588.0	±5%

TOLERANCES UNLESS OTHERWISE NOTED, ALL DIMENSIONS ARE IN INCHES, AND TOLERANCES ARE AS SHOWN HERE. FRACTIONS = $\pm 1/64$ DECIMALS .XX = .01 .XXX = .005 ANGLES = 0°30'		DRAWN JES	DATE 06AUG99	 FENWAL ELECTRONICS 450 Fortune Boulevard, Milford, MA 01757-1745 (508) 478-6000 / FAX (508) 473-6035		
		CHECKED VDJ	DATE 06AUG99			
		APPROVED KJC	DATE 06AUG99	TITLE NTC THERMISTOR OUTLINE		
USED ON ECO 13584		This information is the property of FENWAL ELECTRONICS. It is submitted in confidence, and is not to be disclosed or utilized without written permission.				
SHEET 1	OF 1	DO NOT SCALE DRAWING	SCALE 8:1	SIZE A	DRAWING NUMBER 135-103LZF-J10	REV. G