

# ALS6W10A – ALS6W43A

## Surface Mount Load Dump Transient Voltage Suppressors

**REVERSE VOLTAGE – 10~43 Volts**  
**PEAK PULSE POWER – 4600 Watt**

### FEATURES


- High current capability
- Low Forward Voltage Drop
- Low reverse current
- Low thermal resistance
- Excellent high temperature stability
- Low power loss and high efficiency
- High forward surge capability
- Meet ISO7637-2 and ISO16750-2 surge specification (varied by test condition)
- Meet MSL level 1, per J-STD-020
- LF maximum peak of 260 °C
- AEC-Q101 qualified
- PPAP capable
- Automotive grade
- **Lead-Free Finish; RoHS Compliant (Notes 1 & 2)**
- Halogen and Antimony Free. "Green" Device (Note 3)

### APPLICATION

- High peak power
- High-temperature
- Clamping diode
- Load switching and lighting
- Use in sensitive electronics protection against voltage transients induced by inductive automotive ECU module, especially for automotive load dump protection application

### MECHANICAL DATA

- Case: DO-218 outline plastic package
- Terminals: Matte tin plated, solderable per MIL-STD-750 Method 2026 , J-STD-002 and JESD 22-B102 ④⑤
- Molding Compound Flammability Rating:UL94-0
- High temperature soldering guaranteed: 260°C/10second
- Polarity: Heatsink is anode
- Corresponds to taping packages. (750PCS/Reel)
- Weight: 2.74 grams (Approximate)



### DO-218

DO-218			
Dim.	Min.	TYP.	Max.
A	4.75	5.00	5.25
B	3.66	3.96	4.26
C	1.80	2.00	2.20
D	2.58	2.88	3.18
E	8.20	8.50	8.80
F	9.50	----	10.50
G	----	0.30	----
H	13.20	13.50	13.80
I	8.70	9.00	9.30
J	9.70	10.00	10.25
K	15.00	15.50	16.00
L	2.30	----	3.00

All Dimensions in millimeter

### Primary Characteristics

VWM	10 V to 43 V
VBR	11.1 V to 52.8 V
PPPM (10 x 1000 uS)	4600 W
PPPM (10 x 10 000 uS)	3600 W
IFSM	600 A
Polarity	Uni-directional
Diode variation	Single

### Note:

REV-4, Octo-2021, KSIR07

1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.

2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

**Maximum Ratings (TA = 25 °C unless otherwise noted)**

Parameter			Symbol	Value	Units
Peak pulse power dissipation	10/1000 $\mu$ s waveform		PPPM	4600	W
	10/10 000 $\mu$ s waveform			3600	
Peak forward surge current 8.3 ms single half sine-wave			IFSM	600	A
Operating junction and storage temperature range			TJ, TSTG	-55 to +175	°C


**Electrical Characteristics (TA = 25 °C unless otherwise noted)**

Part Number	Breakdown Voltage V <sub>BR</sub> (V)		Test Current I <sub>T</sub> (mA)	Stand-OFF Voltage V <sub>WM</sub> (V)	Maximum Reverse Leakage at V <sub>WM</sub> I <sub>D</sub> (uA)	Maximum Leakage at V <sub>WM</sub> T <sub>J</sub> = 175 °C I <sub>D</sub> (uA)	Max. Peak Pulse Current at 10/1000 us Waveform (A)	Maximum Clamping Voltage at I <sub>PPM</sub> V <sub>C</sub> (V)
	Min.	Max.						
ALS6W10A	11.1	12.3	5.0	10.0	15	250	271	17.0
ALS6W11A	12.2	13.5	5.0	11.0	10	150	253	18.2
ALS6W12A	13.3	14.7	5.0	12.0	10	150	231	19.9
ALS6W13A	14.4	15.9	5.0	13.0	10	150	214	21.5
ALS6W14A	15.6	17.2	5.0	14.0	10	150	198	23.2
ALS6W15A	16.7	18.5	5.0	15.0	10	150	189	24.4
ALS6W16A	17.8	19.7	5.0	16.0	10	150	177	26.0
ALS6W17A	18.9	20.9	5.0	17.0	10	150	167	27.6
ALS6W18A	20.0	22.1	5.0	18.0	10	150	158	29.2
ALS6W20A	22.2	24.5	5.0	20.0	10	150	142	32.4
ALS6W22A	24.4	26.9	5.0	22.0	10	150	130	35.5
ALS6W24A	26.7	29.5	5.0	24.0	10	150	118	38.9
ALS6W26A	28.9	31.9	5.0	26.0	10	150	109	42.1
ALS6W28A	31.1	34.4	5.0	28.0	10	150	101	45.4
ALS6W30A	33.3	36.8	5.0	30.0	10	150	95	48.4
ALS6W33A	36.7	40.6	5.0	33.0	10	150	86	53.3
ALS6W36A	40.0	44.2	5.0	36.0	10	150	79	58.1
ALS6W40A	44.4	49.1	5.0	40.0	10	150	71	64.5
ALS6W43A	47.8	52.8	5.0	43.0	10	150	66	69.4


**Note:**

4. For all types maximum VF = 1.9V at IF = 100A measured on 8.3ms single half sine-wave.


**FIG.1- Power Derating Curve**




**Fig.3 - Pulse Waveform**




**FIG.5- Typical Transient Thermal Impedance**




**FIG.2- Load Dump Power Characteristics  
(10ms Exponential Waveform)**



**FIG.4- Reverse Power Capability**




**FIG.6- Typical Junction Capacitance**



**Ordering Information :**


Part Number	Case	Packaging
ALS6WxxA	DO-218	750pcs/Reel

**Marking Information :**

LT = Manufacturer's Code Marking  
S6WxxA = Product Type Marking Code  
YXWW = Date Code Marking  
Y = Last Digit of Year (ex: 1 = 2021)  
X = Manufacturer's Internal Code  
WW = Week Code (01 to 53)  
xxxxxx = Assembly Tracking Code  
Cathode Bar

**Packaging Information :**

DEVICE	REEL DIA.	Q'TY/REEL	REEL/BOX	Q'TY/BOX	BOX/CARTON	Q'TY/CARTON	BOX SIZE	CARTON SIZE
	(INCH)	(PCS)	(REEL)	(PCS)	(BOX)	(PCS)	(mm)	(mm)
ALS6WxxA	13	750	1	750	4	3000	360*340*52	382*360*240

**Soldering Pad Layout :**


**IMPORTANT NOTICE**

1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

[www.diodes.com](http://www.diodes.com)