

LUMOTAST 75 IP65, illuminated pushbutton, round collar, flat bezel



description

technical data

> general

| | |
|--|--|
| Collar shape | round |
| Operating temperature, min. | -25 °C |
| Storage temperature, min. | -40 °C |
| Operating temperature, max. | 55 °C |
| Storage temperature, max. | 80 °C |
| illuminated | Yes |
| Lamp socket | T4.5 |
| Packaging | Box |
| Degree of protection, front side, according to DIN EN 60529 | IP65 |
| Environment resistance | IEC 60068-2-14 IEC 60068-2-30 IEC 60068-2-33 IEC 60068-2-78 |
| Protection class | II |
| RoHS compliant | Yes |
| REACH compliant | Yes |

> mounting diameters

| | |
|---------------------------|---------|
| Mounting hole | 16.2 mm |
| Mounting depth | 57.5 mm |
| Installation height | 10.5 mm |
| Outside dimension, length | 19 mm |


direct links

> [RAFI eCatalog](#)

| | |
|--------------------------|----------------------------|
| Outside dimension, width | 19 mm |
| Collar dimension | 19 mm |
| > mechanical data | |
| Operating force, max. | 6.5 N |
| Operating force, min. | 3 N |
| Operating travel, max. | 2.5 mm |
| Contact system | Bridge-snap-action contact |
| Contact material | Silver |
| Fixing | Threaded ring |
| Terminal on the rear | Solder terminal |
| Solderability | Yes |
| > electrical data | |
| Rated voltage, min. | 12 V |
| Rated voltage, max. | 230 V |
| Rated current, min. | 0.05 A |
| Rated current, max. | 4 A |

drawings

Dimensioned drawing



Mounting hole drawing

