





PRODUCT NUMBER

PITCH

T2xx01x100J0G

5.00 mm


 RECOMMENDED P.C.B LAYOUT
 TOP VIEW


Material

- Item ① Clamp : Brass , Ni plated
- Item ② Terminal screw: Steel , Zinc plating "--" slot type
- Item ③ Solder pin : Brass , Tin plated
- Item ④ Terminal housing : Thermoplastic (UL94V-0)

Electrical UL

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 

Dimension A&B

DIM A	Nx5.0
DIM B	(N-1)x5.0

N=Number of poles

Poles	DIMA&B Tolerance
4P-8P	±0.15
9P-14P	±0.25
15P-20P	±0.35
21P-24P	±0.40

PART NO.: T2 xx 0 1 x 1 00J0 G

 Solid Block
 No. of poles
 04 4 poles
 05 5 poles
 ...
 24 24 poles

Body Color	RoHS compliant
0 Black (RAL9005)	(lead<4%)
2 Red (RAL3001/D)	In copper Alloy
3 Orange(RAL2011/P)	
4 Yellow(RAL1018/A)	
5 Green(RAL6018/T)	
6 Blue (RAL5015/A)	
8 Grey(RAL7035/D)	
9 White(RAL1102)	
C Green(RAL6018/U)	

mat'l. code					surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																															
ltr		ecn no		dr	date		tolerances unless otherwise specified					title TERMINAL BLOCK																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
							angles		normal	X.±0.5		RISING CLAMP,3SD WIRE INLET,SOLID TYPE																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
										X.X±0.3		scale																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
							X*±1°			X.XX±0.1		FCI 																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
							dr	EVIN ZHONG		040714		dwg no																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
							engr	EVIN ZHONG		040714		sheet 1 of 1																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
							chr	HANKE FENG		040714		T2xx01x100J0G																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
							appd	SHI JUN		040714		A																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
sheet index		revision sheet		A	1																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																					