
Product Data Sheet

DIN 41612 90° connector strip, Type G, Part No. 111-40264






Illustration similar



Perpendicular



Through Hole



Power



Rugged

- Connection length: 3 mm
- Number of poles: 64
- Premature contact at positions Z2 and Z32
- Soldering Techniques
- Grade 2

» to product on www.ept.de

» to product group DIN 41612

ept GmbH | Bergwerkstr. 50 | 86971 Peiting | Tel. +49 (0) 8861 / 25 01 0 | Fax +49 (0) 8861 / 55 07 | sales@ept.de | **www.ept.de**

Downloaded from Arrow.com.

Product Data Sheet

DIN 41612 90° connector strip, Type G, Part No. 111-40264

Technical Specifications

Basics

Specification	IEC 60603-2 (DIN 41612)
Performance Level	2
No. of Contacts	64
Termination Technology	Soldering Techniques
Termination Length	3 mm
Operating Temperature Range	-55°C to +125°C

Material

Insulator Material	PC, glass-reinforced, UL 94 V-2
CTI value *IEC 60112*	200
Contact Material	copper alloy

Mechanical

Pitch	5.08 x 3.81 mm
Mating Force	100 N
Separating Force per Pin	>0.2 N
Durability	400 insertion cycles

Electrical

Operational Current	5.6 A
Test Voltage	1550 V
Contact Resistance	15 mΩ
Clearance and Creepage	W: ≥ 3.0 mm, L: ≥ 1.6 mm
Insulation Resistance	$>10^6$ MΩ


Approval / Compliance

UL file	E130314
Environment	RoHS compliant

ept GmbH | Bergwerkstr. 50 | 86971 Peiting | Tel. +49 (0) 8861 / 25 01 0 | Fax +49 (0) 8861 / 55 07 | sales@ept.de | **www.ept.de**

Downloaded from Arrow.com.

Derating Diagram





Downloaded from Arrow.com.

Options

Board Lock 90°

Suitable for connectors with type B, C, D, E, F, G male connectors and R female connectors





Type of Insertion	Forces			PCB Thickness	Part Number
	F_m	not soldered F_h	soldered F_h		
Locked	< 30 N	> 10 N	> 20 N	≤ 1.6 mm	111-40264C1
Under Tension	< 30 N	> 7.5 N	> 20 N	> 1.6 mm	

Modifications

Available on request

- Premature contacts
- Special configuration
- Grade I + III or custom
- Custom length

Drawings

Component data for this product you can request through sales@ept.de

Downloaded from Arrow.com.