

MFG PART NUMBER: C10-730191- () () () ()


CODE NUMBER REFERENCE: SLPIRC () P () () ()

ITEM	DESCRIPTION	CODE NUMBER	MFG NUMBER
COLOR	ORANGE	O	0
	BLACK	B	1
	RED	R	2
PIN TYPE	50MM^2 CRIMP	50C	5
	70MM^2 CRIMP	70C	7
	85MM^2 CRIMP	85C	8
	BUSBAR	B	1
	SCREW	T	2
SEALING	IP67(MATED)	S	0
	NO SEALING	N	1
KEYWAY	90°	0	0
	180°	1	1
	60°	2	2
	120°	3	3
	150°	4	4

Screw Type

1. THE REFERENCED PRODUCT IS IN COMPLIANCE WITH THE MAXIMUM CONCENTRATION VALUES (MCVS) AS SET BY RoHS 2.0 DIRECTIVE 2011/65/EU AND ANNEX II AMENDMENT DIRECTIVE (EU)2015/863.

N / A
NEXT ASSEMBLY
METRIC DOCUMENT

UNLESS OTHERWISE SPECIFIED	SPECIFICATIONS	POS	QTY	PART NUMBER	DESCRIPTION	NOTE	
LINEAR DIMENSIONS ARE IN: MILLIMETERS TOLERANCES: ANGLES= $\pm 2^\circ$ DEFAULT LINEAR TOLERANCES SEE TABLE	MATERIAL SPEC. N/A	PARTS LIST					
		APPROVALS		DATE	AMPHENOL INDUSTRIAL OPERATIONS Amphenol Technology(Zhuhai)Co.,Ltd No.63, Xingnan Road, Sanzao Town, Jinwan, Zhuhai, PRC		
		PREPARED BY	ALAN ZHANG	Nov-13-16			
		ENGINEER IN CHARGE	SEVEN XIE				
		DESIGN MANAGER	ROB WENG				
		DESIGN ACTIVITY GROUP	C&I	10.3MM SURLOK PLUS RECEPTACLE			
DIM. & TOL. PER ASME Y14.5M-1994; DRM PER MIL-DTL-31000; OTHER AMPHENOL STANDARDS: 9-9318	PROCESS SPEC. N/A	THIRD ANGLE PROJECTION					
LEGENDS:  FLAG NOTE CALL OUT REFERENCE ONLY				SIZE C	CAGE CODE 77820	DOCUMENT NO. C10-730191-()	REV. G
				SCALE: 1:0	REF.	SHEET I OF I	

REV
G