





SYMBOL DEFINITION			MISSING SYMBOLS		DWG STATUS				ZONE	REVISION HISTORY			AUTH	DR	APVD		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.			TOTAL NO OF INSPECTIONS REQUIRED	8	NO MISSING SYMBOL NUMBER	DATE	STG	REV	N/P	CHG	RELEASED - WAS 12162539	256020	RJD	RJD	WGR	1	2
			LAST NO. USED	8													



15492503 NUT: (T-NUT MAY BE ASSEMBLED FROM TOP OR BOTTOM OF CONVENIENCE CTR)

12162366 CONVENIENCE CTR



SCALE 1:1

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATING COMPONENTS:
 - FUSE CAVITIES ACCEPT TERMINAL 12004552 OR EQUIVALENT
 - RELAY CAVITIES ACCEPT TERMINAL 12015838 OR EQUIVALENT
 - SECONDARY TERMINAL LOCK 12015225 OR EQUIVALENT
 - COVER 12162522 OR EQUIVALENT
- T-NUT MUST NOT ROTATE IN CONNECTOR WHEN ASSEMBLED WITH MATING CONNECTOR USING A TORQUE OF 11.3 NM
- THE T-NUT MUST WITHSTAND A MINIMUM PUSH-OUT FORCE OF 980 NEWTONS (220 POUNDS)

DIMENSIONAL RANGE (MM)		TOLERANCE UNLESS OTHERWISE SPECIFIED		CHART LET	
FROM	TO				
0	20	±0.2	±0.3	±0.4	±0.5
20	30	±0.3	±0.4	±0.5	±0.6
30	40	±0.4	±0.5	±0.6	±0.8
40	50	±0.5	±0.6	±0.8	±1.0
50	60	±0.6	±0.8	±1.0	±1.2
60	70	±0.8	±1.0	±1.2	±1.5
70	80	±1.0	±1.2	±1.5	±2.0
80	90	±1.2	±1.5	±2.0	±2.5
90	100	±1.5	±2.0	±2.5	±3.0
100	150	±2.0	±2.5	±3.0	±4.0
150	200	±2.5	±3.0	±4.0	±5.0
200	250	±3.0	±4.0	±5.0	±6.0
250	300	±4.0	±5.0	±6.0	±8.0
300	400	±5.0	±6.0	±8.0	±10.0

DELPHI		DELPHI PACKARD ELECTRIC SYSTEMS		WARREN, OH	
DRAWING NAME		ASM CENT CONV CTR		BLK PRINTED	
DRAWING NUMBER		15492624			
SIZE	SCALE	FRAME NO	SHEET NO	STG REV	N/P
A0	2:1	1	1	1	1