

QT-Brightek Chip LED Series

0402 SMD Chip LED

Part No.: QBLP595-IW-2897

2897: High Bright

Product: QBLP595-IW-2897	Date: February 13, 2026	Page 1 of 10
	Version# 1.1	

Table of Contents:

Introduction 3

Electrical / Optical Characteristic (Ta=25 °C) 4

Absolute Maximum Rating 4

Correlated Color Temperature Chart 5

Characteristic Curves..... 6

Solder Profile & Footprint..... 7

Packing 8

Labeling 9

Ordering Information 9

Revision History 10

Disclaimer 10

Introduction

Feature:

- Yellow diffused lens
- Package in tape and reel
- Compact 0402 package
- InGaN technology
- Viewing angle: 150° typ.
- Height profile: 0.5mm

Application:


- Status indication
- Back lighting application

Certification & Compliance:

- ISO9001
- RoHS Compliant



Dimension:



Units: mm / tolerance = +/-0.1mm

Product: QBLP595-IW-2897	Date: February 13, 2026	Page 3 of 10
	Version# 1.1	

Electrical / Optical Characteristic (Ta=25 °C)

Product	Color	I _F (mA)	V _F (V)		CCT Coordinate	I _v (mcd)	
			Typ.	Max.		Min.	Typ.
QBLP595-IW-2897	White	20	3.1	3.7	X=0.33 Y=0.33	250	420

Absolute Maximum Rating

Material	P _d (mW)	I _F (mA)	I _{FP} (mA)*	V _R (V)	T _{OP} (°C)	T _{ST} (°C)	T _{SOL} (°C)**
InGaN	111	30	100	5	-40 ~ +80	-40 ~ +85	260

*Duty 1/10 @ 1KHz

**IR Reflow for no more than 10 sec @ 260 °C


Forward Voltage V_F @ I_F=20mA

Bin	Min.	Max.	Unit
f	2.8	3.1	V
g	3.1	3.4	
h	3.4	3.7	

Luminous Intensity I_v @ I_F=20mA







Bin	Min.	Max.	Unit
N	250	320	mcd
O	320	400	
P	400	500	
Q	500	630	
R	630	800	

Correlated Color Temperature Chart




Rank	Chromaticity coordinates				
A1	X	0.3	0.3	0.32	0.32
	Y	0.3	0.33	0.36	0.33
A2	X	0.3	0.3	0.32	0.32
	Y	0.27	0.3	0.33	0.3
A3	X	0.3	0.3	0.32	0.32
	Y	0.24	0.27	0.3	0.27
B1	X	0.32	0.32	0.34	0.34
	Y	0.33	0.36	0.39	0.36
B2	X	0.32	0.32	0.34	0.34
	Y	0.3	0.33	0.36	0.33
B3	X	0.32	0.32	0.34	0.34
	Y	0.27	0.3	0.33	0.3
C1	X	0.34	0.34	0.36	0.36
	Y	0.36	0.39	0.42	0.39
C2	X	0.34	0.34	0.36	0.36
	Y	0.33	0.36	0.39	0.36
C3	X	0.34	0.34	0.36	0.36
	Y	0.3	0.33	0.36	0.33

Characteristic Curves




Solder Profile & Footprint

-The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):




Recommended Pad Layout



Units: mm


Packing

Reel Dimension:




(Unit: mm)

Tape Dimension:




(Unit: mm)

Arrangement of Tape:



Packaging Specifications:



Ordering Information

Product: QBLP595-IW-2897	Date: February 13, 2026	Page 9 of 10
	Version# 1.1	



Revision History

Description:	Revision #	Revision Date
New Release of QBLP595-IW-2897	V1.0	02/09/2018
Drawing redrafted for clarity and documentation consistency; no changes to form, fit, or function.	V1.1	02/13/2026

Disclaimer

QT-BRIGHTTEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. QT-BRIGHTTEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

Life Support Policy

QT-BRIGHTTEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of QT-BRIGHTTEK. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Product: QBLP595-IW-2897	Date: February 13, 2026	Page 10 of 10
	Version# 1.1	