



main menu



home

test & measurement

products

skills

download

online catalogue T&M

clamp-type test probes

crocodile clips

test probes

oscilloscope test probes

measuring leads

- ▶ 0,64 mm system
- ▶ 2 mm system
- ▶ 2 mm safety system
- ▶ 4 mm system
- ▶ 4 mm sliding sleeve system
- ▶ 4 mm safety system
- ▶ test accessories

plugs

sockets

sets

miscellaneous

company

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

terms and conditions

Home ▶ measuring leads ▶ measuring leads ▶ MLS WS 200/1

MLS WS 200/1

 datasheet for MLS WS 200/1
 article number: 934069101


View Full-Size Image



search online catalogue

Search

Search

Messetermine

No events

QR-Code



product description:	order number: 934 069-101
description:	Safety measuring lead to IEC 61010 standard, at either end 4 mm diameter safety connector with onward connection capability (4mm socket). Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, shatter-proof grip sleeve and lead. Built in color indicator for easy indentification of insulation damages.
typ:	MLS WS 200/1 rot/red
system:	4 mm safety system
order number:	934 069-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT II
pin dimensions	4 mm
type of contact:	pin (spring loaded)
cable type:	LEH-XY
cable specification:	highly flexible lead
wire stranding:	259 x 0.07 mm
rated voltage:	AC/DC 1000 V
rated current:	16 A
Please consider derating curve!	
contact resistance:	40 mOhm
cable length:	200 cm
conductor size:	1 mm²
cable material:	PVC
cable color:	red
material	
contact material:	contact pin: brass contact spring: copper - beryllium
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	-15 °C to +70 °C
flammable class:	
housing (basic material):	UL 94 V - 2
drawing	