





P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI6727	13JUNE2000	-	RDR
	A	REVISED PER E.O.P20196	07MAY2009	-	RDR
	B	REVISED PER E.O.P20274	09SEPT2009	-	RDR
	C	REVISER PER PCN-24-226269	06JAN2025	AJT	MB

3D VIEW




△ MATERIAL: RECEPTACLE: PA66 GF15, GRAY
CAP: PA66 GF15, BLACK
WEDGELOCK (INCLUDED): PBT GF30 (GREEN)
BUSBAR: COPPER ALLOY, NICKEL PLATED.

3. THE 8 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 52 AMPS.

2. ORIENTATION OF "DEUTSCH" AND "-P021" TO BE OPTIONAL.

① MATES WITH DT06-08SA-XXXX (XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR MODIFICATIONS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. MCCORD 23APR2009		 TE Connectivity									
DIMENSIONS: INCHES [mm]		CHK -											
		APVD -		NAME DT 8 WAY RECEPTACLE KEY ARRANGEMENT A 8 PIN BUSBAR-NICKEL PLATED COLOR; GREY									
		PRODUCT SPEC 108-151009											
		APPLICATION SPEC 114-151009											
		WEIGHT -											
MATERIAL 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±025[0,63] 4 PLC ± ANGLES ±		SIZE A3		CAGE CODE 00779	DRAWING NO C-DT04-08PA-P021		RESTRICTED TO -				
		FINISH -		CUSTOMER DRAWING						SCALE 2:1	SHEET 1	OF 1	REV C