






REV.	DATE	DESCRIPTION
NC	03/08/05	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .187"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .310 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
8						DRAWN	G.R.S.	03/08/05										
7						CHECKED				PART DESCRIPTION BNC CRIMP JACK (FOR B573945, Q841 MINI MAX 500 CABLE)								
6						ISSUED												
5	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1				PART NO. 112638							
4	SLEEVE	DELFIN	NATURAL	1														
3	INSULATOR	DELFIN	NATURAL	1														
2	CONTACT PIN	PHOS. BRONZE	GOLD	1														
1	HOUSING/BODY	BRASS	NICKEL	1														
DESCRIPTION		MATERIAL	FINISH	QTY	CAD FILE C:/112/112638.DWG				DWG NO.		112638.DWG		REV.	NC	SIZE	A	SCALE	NA