



NOTES:

1. TO BE USED WITH #22-#28 AWG STRANDED WIRE WITH (1.35)/.053 DIA. MAX. INSULATION.
2. STANDARD PACKAGING FOR GROUPED HOUSING ASSEMBLIES PER PK-70873-0215.
3. TERMINALS ARE SHOWN PRE-LOADED INTO HOUSING AND LOCKED INTO THE FIRST ROW OF WINDOWS.
4. ALL DIMENSIONS ARE REFERENCE ONLY.
5. SEE DWG. SD-70066-**** FOR OPTIONAL HOUSING DETAILS.
6. REFER TO PRODUCT SPECIFICATION PS-70400.
7. FOR ACCOUNTING PURPOSES ONLY, ONE EDP ORDER NUMBER REPRESENTS ONLY ONE HOUSING OF ANY GIVEN CHAINED COMBINATION OF CKT. SIZES.

PLATING CODES:

- 164 - .000150 MIN. TIN/LEAD PLATE OVER NICKEL PLATE.
- 571 - .000015 MIN. GOLD PLATE IN SELECTED AREA, .000075 MIN. TIN/LEAD PLATE IN SELECTED AREA, OVER NICKEL PLATE OVERALL.
- 574 - .000030 MIN. GOLD PLATE IN SELECTED AREA, .000075 MIN. TIN/LEAD PLATE IN SELECTED AREA, OVER NICKEL PLATE OVERALL.
- P164 - .000150 MIN. TIN/LEAD PLATE OVER MIN. NICKEL PLATE. (PRE-PLATE)

PLATING CODE (STRIPE ON CARRIER STRIP)

PLATING	COLOR
164	NONE
571	YELLOW
574	RED
P164	NONE

I.D. SLOT/WIRE GAUGE CHART

SLOT I.D.	SLOT SIZE	WIRE GAUGE
A	.015 ±.002/(0.38 ±0.05)	24 AWG - STRANDED
B	.011 ±.002/(0.28 ±0.05)	26 AWG - STRANDED
C	.0075 ±.002/(0.19 ±0.05)	28 AWG - STRANDED
D	.019 ±.002/(0.48 ±0.05)	22 AWG - STRANDED

E9	ADD -7713,7723 ECR UDT2000-1190 KMS 05/30/2000	E6	ADD CARRIER CHAMF ECN #UDT1998-0280 05/20/98 LMGRATH
E8	SHT 4, ADD: P/N-0074 UDT 2000-0605 GIZOWSKI 12-29-99	E5	ADDED PARTS ECR #U7-0423 MCFARLAN 96-10-16
E7	REL-0071, 72, 73 UDT 1999-0371 SCHAFER 11-13-9	E4	ADDED ENG* -0063 ECR# U7-0283 MCFARLAN 96-9-17
LTR.	REVISIONS	LTR.	REVISIONS

DIMENSIONS SHOWN (METRIC) INCH
UNLESS OTHERWISE SPECIFIED
TOLERANCES: ANGULAR ± 1/2°

3 PLACE ±	INCH	METRIC
2 PLACE ±		
1 PLACE ±		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DRW: MGB CHK'D: MJM
APP'D: MJM SCALE: 4 : 1

▽ = 0 ▼ = 0 REVISE ONLY ON CAD SYSTEM

TITLE: ASSEMBLY, CONNECTOR BOX I.D. SINGLE ROW/.100 GRID GROUPED HOUSINGS

MOLEX INCORPORATED SHEET NO. DATE
LISLE, ILL. 60532 U.S.A. 1 OF 4 11/20/89

SEE CHART SDA-70977-****

FILE NAME: ST0977X1 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION. DA C

ONE EDP NUMBER REPRESENTS ONE INDIVIDUAL HOUSING (SEE NOTE 7)

EDP. NUMBER	ENG. NUMBER	DIM. "A" (MAX.)	DIM. "B" (MAX.)	OPTION	CIRCUIT SIZE	NUMBER OF HOUSINGS IN TOTAL ASSEMBLY	HOUSING NO.	TERMINAL NO.	PLATING	WIRE SIZE
014-60-7022	A-70977-0001	1.999 (50.77)	.199 (5.05)	G	2	10	70066-0176	70028-0005	164	24 AWG
014-60-7023	A-70977-0002	1.999 (50.77)	.199 (5.05)	G	2	10	70066-0176	70028-0007	164	26 AWG
014-60-7034	A-70977-0003	2.399 (60.93)	.299 (7.59)	A	3	8	70066-0037	70028-0030	164	22 AWG
014-60-7032	A-70977-0004	1.199 (30.45)	.299 (7.59)	G	3	4	70066-0177	70028-0005	164	24 AWG
014-60-3027	A-70977-0005	.599 (15.21)	.199 (5.05)	A	2	3	70066-0036	70028-0005	164	24 AWG
014-60-4021	A-70977-0006	.599 (15.21)	.199 (5.05)	A	2	3	70066-0036	70028-0007	164	26 AWG
014-60-4025	A-70977-0007	.599 (15.21)	.199 (5.05)	A	2	3	70066-0036	70028-0009	164	28 AWG
014-62-4029	A-70977-0008	.599 (15.21)	.199 (5.05)	A	2	3	70066-0036	70028-0011	571	24 AWG
014-62-5023	A-70977-0009	.599 (15.21)	.199 (5.05)	A	2	3	70066-0036	70028-0013	571	26 AWG
014-62-5027	A-70977-0010	.599 (15.21)	.199 (5.05)	A	2	3	70066-0036	70028-0015	571	28 AWG
014-62-6021	A-70977-0011	.599 (15.21)	.199 (5.05)	A	2	3	70066-0036	70028-0017	574	24 AWG
014-62-6025	A-70977-0012	.599 (15.21)	.199 (5.05)	A	2	3	70066-0036	70028-0019	574	26 AWG
014-62-6029	A-70977-0013	.599 (15.21)	.199 (5.05)	A	2	3	70066-0036	70028-0021	574	28 AWG
014-60-3028	A-70977-0014	.599 (15.21)	.199 (5.05)	C	2	3	70066-0071	70028-0005	164	24 AWG
014-60-4022	A-70977-0015	.599 (15.21)	.199 (5.05)	C	2	3	70066-0071	70028-0007	164	26 AWG
014-60-4026	A-70977-0016	.599 (15.21)	.199 (5.05)	C	2	3	70066-0071	70028-0009	164	28 AWG
014-62-5020	A-70977-0017	.599 (15.21)	.199 (5.05)	C	2	3	70066-0071	70028-0011	571	24 AWG
014-62-5024	A-70977-0018	.599 (15.21)	.199 (5.05)	C	2	3	70066-0071	70028-0013	571	26 AWG
014-62-5028	A-70977-0019	.599 (15.21)	.199 (5.05)	C	2	3	70066-0071	70028-0015	571	28 AWG
014-62-6022	A-70977-0020	.599 (15.21)	.199 (5.05)	C	2	3	70066-0071	70028-0017	574	24 AWG
014-62-6026	A-70977-0021	.599 (15.21)	.199 (5.05)	C	2	3	70066-0071	70028-0019	574	26 AWG
014-62-7020	A-70977-0022	.599 (15.21)	.199 (5.05)	C	2	3	70066-0071	70028-0021	574	28 AWG
014-60-3029	A-70977-0023	.599 (15.21)	.199 (5.05)	D	2	3	70066-0106	70028-0005	164	24 AWG
014-60-4023	A-70977-0024	.599 (15.21)	.199 (5.05)	D	2	3	70066-0106	70028-0007	164	26 AWG
014-60-4027	A-70977-0025	.599 (15.21)	.199 (5.05)	D	2	3	70066-0106	70028-0009	164	28 AWG

70977

MFG. SH. REV.

B		SEE SHEET I	<small>DIMENSIONS SHOWN (METRIC) INCH</small> <small>UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°</small> <table border="1"> <tr><th>3 PLACE</th><th>±</th><th>---</th><th>---</th></tr> <tr><th>2 PLACE</th><th>±</th><th>---</th><th>---</th></tr> <tr><th>1 PLACE</th><th>---</th><th>---</th><th>---</th></tr> </table>	3 PLACE	±	---	---	2 PLACE	±	---	---	1 PLACE	---	---	---
3 PLACE	±	---		---											
2 PLACE	±	---	---												
1 PLACE	---	---	---												
A I		SEE SHEET I													
E	SEE SHEET I	A	SEE SHEET I												
LTR.	REVISIONS	LTR.	REVISIONS												

<small>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</small> DRWG. BY: AAB APP'D. BY: MJM CHK'D. BY: SCALE:	DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2° 3 PLACE ± --- --- 2 PLACE ± --- ± --- 1 PLACE --- ± --- DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	TITLE: ASSEMBLY, CONNECTOR BOX I.D SINGLE ROW - .100 GRID GROUPED HOUSINGS MFG. MOLEX INCORPORATED L1SLE,ILL. 60532 U.S.A. SHEET NO. 2 DATE 01/18/91 PART NO. SEE CHART DRWG. NO. SDA-70977-*** THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.
--	--	---