
Part Number : 530481110
Product Description : 1.25mm Pitch, PicoBlade PCB Header, Single Row, Right-Angle, Through Hole, Tin (Sn) Plating, Friction Lock, 11 Circuits, Tray, 2.30mm PC Tail Length
Series Number : 53048
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

530481110_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

530481110.dxf

Specifications

510210000-AS-000.pdf

SPK-53048-001-001.pdf

510211010-PS-000.pdf

510211111-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-

Downloaded from Arrow.com.

	DC (05 Nov 2025) SCIP:9b57ad9e-307b-418e-a95f-35bbea3c472a
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	53048
Description	1.25mm Pitch, PicoBlade PCB Header, Single Row, Right-Angle, Through Hole, Tin (Sn) Plating, Friction Lock, 11 Circuits, Tray, 2.30mm PC Tail Length
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	PicoBlade
UPC	800753750210

Agency

UL	E29179

Downloaded from Arrow.com.

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Physical

Breakaway	No
Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	3.50mm
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	255.670/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.80mm
PC Tail Length	2.30mm
Pitch - Mating Interface	1.25mm
Plating min - Termination	0.900µm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	51021

Downloaded from Arrow.com.